

# Ground Rod Clamp, Rod to Conductor, Bronze



## CERTIFICATIONS



## FEATURES

For use with copper-bonded ground rods

Parts that are UL 467 Listed are suitable for direct burial in earth or concrete

## SPECIFICATIONS

Table 1/2


| Catalog Number | Article Number | Material       | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual (Ø) | Conductor Size                                                                 | Wrench Size |
|----------------|----------------|----------------|------------------------------|---------------------------------|--------------------------------------------------------------------------------|-------------|
| CP38           | 158155         | Silicon Bronze | 3/8"                         | 9.7 mm                          | #10 Solid - #2 Stranded, 6 mm <sup>2</sup> Solid - 25 mm <sup>2</sup> Stranded | 9/16"       |
| C12            | 158260         | Gunmetal       | 1/2"                         | 12.5 - 12.7 mm                  | 50 mm <sup>2</sup> Stranded Max                                                | 14 mm       |
| CP58           | 158165         | Silicon Bronze | 1/2" - 5/8"                  | 12.5 - 14.2 mm                  | #10 Solid - #2 Stranded, 6 mm <sup>2</sup> Solid - 25 mm <sup>2</sup> Stranded | 3/4"        |

| CatalogNumber | Article Number | Material       | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual (Ø) | Conductor Size                                                                  | Wrench Size |
|---------------|----------------|----------------|------------------------------|---------------------------------|---------------------------------------------------------------------------------|-------------|
| C58           | 158160         | Gunmetal       | 1/2" - 5/8"                  | 12.5 - 15 mm                    | 70 mm <sup>2</sup> Stranded Max                                                 | 14 mm       |
| C19           | 156900         | Gunmetal       | 5/8" - 3/4"                  | 14.2 - 19 mm                    | 70 mm <sup>2</sup> Stranded Max                                                 | 14 mm       |
| C200          | 156910         | Gunmetal       | 5/8" - 3/4"                  | 14.2 - 20 mm                    | 70 mm <sup>2</sup> Stranded Max                                                 | 24 mm       |
| C34           | 158170         | Gunmetal       | 5/8" - 3/4"                  | 14.2 - 17.2 mm                  | 70 mm <sup>2</sup> Stranded Max                                                 | 14 mm       |
| HDC1          | 158250         | Silicon Bronze | 1"                           | 25.4 mm                         | #8 Solid - 4/0 Stranded, 10 mm <sup>2</sup> Solid - 95 mm <sup>2</sup> Stranded | 13/16"      |

Table 2/2

| Catalog Number | Article Number | Complies With   | Torque (TQ)      | Certifications            |
|----------------|----------------|-----------------|------------------|---------------------------|
| CP38           | 158155         |                 | 16.90 - 25.4 N·m | UL                        |
| C12            | 158260         |                 | 25 N·m Max       |                           |
| CP58           | 158165         | IEC® EN 62561-1 | 16.90 - 25.4 N·m | UL, CSA-US, RUS, CSA, cUL |
| C58            | 158160         | IEC® EN 62561-1 | 25 N·m Max       |                           |
| C19            | 156900         |                 | 25 N·m Max       |                           |
| C200           | 156910         |                 | 25 N·m Max       |                           |
| C34            | 158170         | IEC® EN 62561-1 | 25 N·m Max       |                           |
| HDC1           | 158250         |                 | 50.8 N·m         | UL, cUL                   |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE