

Inspection Housing, Polyolefin



These inspection housings are engineered to be a durable, lightweight solution for providing protection and access to vital utility infrastructure. The lightweight design allows for safer installations while the uniquely strong material blend and construction does not sacrifice critical performance.

FEATURES

Lightweight design and multiple handholes allow for easy handling and installation by one person

Durable, single-piece body engineered to resist bowing during installation and withstand heavy loads

Unique material blend resists chipping and cracking

ANSI/SCTE 77 Tier 15 Design Load of 15,000 lbs (6,804 kg) with a test load of 22,500 lbs (10,206 kg)

Includes the words "GROUND" on the cover

SPECIFICATIONS

Material: Polyolefin

Table 1/1

Catalog Number	Height	Length	Width	Unit Weight
IH1250D	305 mm	305mm	305 mm	5.58 kg
IH1250F	584 mm	305mm	305 mm	17.28 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE