

# ISOnV Conductor Support Block



## FEATURES


Weighted ballast with cable fastener to support ISOnV Insulated Conductor along rooftop

## SPECIFICATIONS

Table 1/1

| Catalog Number    | Finish                | Material                                                  | Diameter (Ø) | Height 1 (H1) | Height 2 (H2) | Unit Weight |
|-------------------|-----------------------|-----------------------------------------------------------|--------------|---------------|---------------|-------------|
| ISONVBLOCK4K<br>G | Hot-Dip<br>Galvanized | Concrete,<br>Stainless Steel<br>304 (EN<br>1.4301), Steel | 215 mm       | 80mm          | 140mm         | 4 kg        |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**