

Rebar Grounding Clamp, Heavy Duty



CERTIFICATIONS



FEATURES

Provides two connection points to concrete encased electrodes (rebar) for states where the Authority Having Jurisdiction (AHJ) requires it

Meets 2005 NEC® standard requirement for bonding to rebar into the grounding system

Suitable for direct burial applications

Has high-strength bronze alloy construction

Easy to install

SPECIFICATIONS


Material: Bronze

Table 1/1

Catalog Number	Article Number	Conductor Size	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Certifications
RC70	710325	#8 Solid - 2/0 Stranded, 10 mm ² Stranded - 70 mm ² Stranded	8 - 18 mm	#3 - #6	10M - 20M	UL

CatalogNumber	Article Number	Conductor Size	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Certifications
RC100	710335	#8 Solid - 4/0 Stranded, 10 mm² Stranded - 100 mm² Stranded	18 - 36 mm	#6 – #11	20M – 35M	UL, cUL

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE