

Special Track Work Mold Only, Power



FEATURES

Replacement molds designed for bonding structures in power bond applications

To be used with factory-formed terminals

Available in either left or right-hand orientation

SPECIFICATIONS

Rail Type: Crane Rail Profiles

Material: Graphite

Bond Terminal Style: J

Table 1/1

Catalog Number	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBJT503LHM	2/0 Concentric	10.62mm	T5	Left Hand
PBJT503RHM	2/0 Concentric	10.62mm	T5	Right Hand
PBJT52QLHM	4/0 Concentric	13.41mm	T5	Left Hand
PBJT52QM	4/0 Concentric	13.41mm	T5	Left and Right Hand
PBJT52QRHM	4/0 Concentric	13.41mm	T5	Right Hand

Catalog Number	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBJT52WLHM	250 kcmil Ropelay	19.05mm	T5	Left Hand
PBJT52WM	250 kcmil Ropelay	19.05mm	T5	Left and Right Hand
PBJT52WRHM	250 kcmil Ropelay	19.05mm	T5	Right Hand

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE