

BD Crimp and Drill Tool



CERTIFICATIONS



FEATURES

For crimping and drilling of braid terminals

Use with FRCB Flat Braid in Coil, Plain Copper and FTCB Flat Braid in Coil, Tinned Copper

Includes guide and drill bit

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Cross Section	Drill Bit Diameter	Screw Diameter	Unit Weight
BD16-8	558640	16mm ²	8.5 mm	8	0.65 kg
BD16	558610	16mm ²	6.5 mm	6	0.65 kg
BD25	558620	25mm ²	11 mm	10	0.68 kg
BD50	558630	50mm ²	12.5 mm	12	0.71 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE