

Neutral Bar for TD Distribution Blocks



CERTIFICATIONS



FEATURES

Attaches to four pole distribution blocks for increased wire capacity

Direct electrical connection

Strong mechanical assembly

Transparent protection cover

Halogen free

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

SPECIFICATIONS

Catalog Number	NB-125A	NB-160A
Article Number	563841	563201
Max Current Rating, IEC	125A	160A
Short Term Withstand Current (Icw) 1s	4.5kA	6.2kA
Peak Short Circuit Current (Ipk)	30kA	35kA

Catalog Number	NB-125A	NB-160A
Line Side Number of Connections	3	4
Line Side Compact Stranded Wire Size	10 - 25 mm ²	10 - 35 mm ²
Line Side Stranded Wire Size - Ferrule	6 - 16 mm ²	10 - 25 mm ²
Load Side Number of Connections	9	10
Load Side Compact Stranded Wire Size	2,5 - 6 mm ²	2,5 - 16 mm ²
Load Side Stranded Wire Size - Ferrule	1,5 – 6 mm ²	1,5 – 16 mm ²
Depth (D)	37.4mm	41.4mm
Height (H)	34.3 mm	34.3 mm
Width (W)	142 mm	170 mm
Unit Weight	0.17 kg	0.2 kg
For Use With	TD-100-125AL (563830) TD-100-125ALL (563840)	TD-160A (563200) TD-160AL (563990)
Flammability Rating	UL® 94V-0	UL® 94V-0
Complies With	IEC® 60947-7-1	IEC® 60947-7-1

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE