

nVent ERIFLEX Flexidrill Drill Guide



CERTIFICATIONS



FEATURES

Guide for drilling holes into nVent ERIFLEX Flexibar, PBC Braided Power Shunts and PPS Presswelded Power Shunts

Includes dies for mutiple diameters

Adjustable guides allow for multiple hole center to hole center distances

RoHS compliant

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Die Hole Size	Depth	Height	Width
FLEXIDRILLR	558600	Steel	6.5 mm, 8.5 mm, 10.5 mm, 12.5 mm	300mm	150 mm	250 mm

Table 2/2

Catalog Number	Article Number	Unit Weight
FLEXIDRILLR	558600	9.5 kg

ADDITIONAL PRODUCT DETAILS

Do not use with nVent ERIFLEX Flexibar Summum.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE