

nVent ILSCO TaskMaster® Tools - 12-Ton Crimping Tool



nVent ILSCO TaskMaster - 12-Ton Pistol Grip Crimping Tool is a crimping tool that can be used with the nVent ERICO Compression Grounding Connectors line. The C, and E crimps are compatible with this tool in addition with the nVent ILSCO Dies.

With the 12-Ton Pistol Grip Crimping Tool, it is very easy to create secure connections that can be made in a matter of minutes, due to its powerful features like 360-degree tool head rotation, dual speed pump and a variable speed trigger. To make the tool even more user-friendly it also comes with a left and right-handed manual release, LED work light and battery charge indicator.

The 12-Ton Pistol Grip Crimping Tool is powered by an 18-volt battery platform cordless system providing a combination of professional grade power, light-weight and high-performance for all day use.

FEATURES

12-Ton Crimping tool with carrying case, without battery and charger

The 12-Ton Pistol Grip Crimping Tool is designed to be versatile for many different job site applications and conductor configurations

Quick and easy crimping due to ergonomic design and convenient usage features

Compatible with nVent ILSCO ILD-Dies for crimping nVent ERICO Compression Crimp Connectors - C-crimps, E-crimps

Compliance for Power & Grounding: Tested in conjunction with dies and connectors in accordance to UL467 and UL486A/B standards

Tool is interchangeable with other manufacturers dies

SPECIFICATIONS

Table 1/1

Catalog Number	Material	Conductor Material	Length	Width	Height	Unit Weight
TB-12U1000-PX	Steel, Plastic	Copper	431mm	304 mm	76.2 mm	7.21 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE