

19-inch Power Distribution Unit, HPDS



Easy to mount strip with several power sockets for situations when external equipment need to be plugged in. For 19" profiles.

FEATURES

Description: With or without ON/OFF switch. Including 2 m cable with right angle plug. 19" assembly brackets can be turned by 90°. Outlets 35° turned.

Material: Aluminium extrusion, anodized. Outlets polyamide 6.6, RAL 7035. Nickel plated earth contacts.

Cable with angle plug: 2 m x 1.5 mm², Schuko.

Rated power: 16 A / 3600 W.

Earthing: Double earthing.

Delivery: 1 complete PDU with power cable and 19" assembly brackets and fixing kit.

SPECIFICATIONS

Material:	Aluminum
Color:	Light Gray
Over Voltage Protection:	No
Finish:	Powder Coated
Color Code:	RAL 7035

Table 1/1						
Catalog Number	Height	Width	Depth	On/Off Switch Included	Socket Quantity	Socket Type
HPDS119009	60mm	485mm	28mm	No	9	SCHUKO 250 V / 16 A
HPDS119108	60mm	430mm	28mm	Yes	8	SCHUKO 250 V / 16 A

ADDITIONAL PRODUCT DETAILS

HPDS 119009 (height units); 119009 (with 19"); 119009 (0=no switch, 1=switch 2=over-voltage protection); 119009 (no. of outlet). Note: UK supplies UK sockets.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE