

Connection Terminal Plate, W060



Connection terminal plate for many different conductor types.

INDUSTRY STANDARDS

UL

CSA

GL

FEATURES

Description: Connection terminal plate, 3-pole, with cover cap.

For busbars: 12, 15, 20, 25, 30 × 5, 10.

Rated voltage: 690 V

Rated peak withstand current I_{pk} max: 40.5 kA (01240), 56.3 kA (01243)

Pack quantity: 1 pc.

Approvals: CSA, UL, GL

SPECIFICATIONS

Table 1/1						
Catalog Number	Height	Width	Depth	Material	Finish	Color
01240	54mm	25mm	32mm	Plastic	Textured	Light Gray
01243	81mm	25mm	32mm	Plastic	Textured	Light Gray

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE