

Plain Doors, DN



This door replaces the rear panel in a floor standing enclosure to allow for rear access of equipment installed in the front, or for using back to back mounting plates to increase the enclosure's mounting space.

FEATURES

Description: Standard door equipped with double-bit 3 mm lock system and door frame. Door accessory kit DNMK (hinges, rod catches) to be ordered separately. Allows all the options of the locking program and 180° hinges. Compatible with combinable and compact enclosure ranges.

Material: 2 mm steel plate.

Maximum load: 800 N.

Finish: RAL 7035 structured powder coating.

Mounting requirements: Use hinge kit DNMK if no door was fitted previously.

Pack quantity: 1 piece.

SPECIFICATIONS

Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Door Type	Enclosure Material
DN2210R5		2182mm	993mm	17mm	Plain	Mild Steel
DN1106R5		1082mm	593mm	17mm	Plain	Mild Steel
DN1206LR5		1182mm	593mm	17mm	Left Door	Mild Steel
DN1206R5		1182mm	593mm	17mm	Plain	Mild Steel
DN1206RR5		1182mm	593mm	17mm	Right Door	Mild Steel
DN1208R5		1182mm	793mm	17mm	Plain	Mild Steel
DN1405LR5		1382mm	493mm	17mm	Left Door	Mild Steel
DN1405RR5		1382mm	493mm	17mm	Right Door	Mild Steel
DN1406LR5		1382mm	593mm	17mm	Left Door	Mild Steel
DN1406R5	DN1406R5	1382mm	593mm	17mm	Plain	Mild Steel
DN1406RR5		1382mm	793mm	17mm	Right Door	Mild Steel
DN1408R5	DN1408R5	1382mm	793mm	17mm	Plain	Mild Steel
DN1606LR5	DN1606LR5	1582mm	593mm	17mm	Left Door	Mild Steel
DN1606R5	DN1606R5	1582mm	593mm	17mm	Plain	Mild Steel
DN1606RR5	DN1606RR5	1582mm	593mm	17mm	Right Door	Mild Steel
DN1608R5	DN1608R5	1582mm	793mm	17mm	Plain	Mild Steel

Catalog Number	Article Number	Height	Width	Depth	Door Type	EnclosureMaterial
DN1610R5	DN1610R5	1582mm	993mm	17mm	Plain	Mild Steel
DN1804LR5	DN1804LR5	1782mm	393mm	17mm	Left Door	Mild Steel
DN1804RR5	DN1804RR5	1782mm	393mm	17mm	Right Door	Mild Steel
DN1805LR5	DN1805LR5	1782mm	493mm	17mm	Left Door	Mild Steel
DN1805R5	DN1805R5	1782mm	493mm	17mm	Plain	Mild Steel
DN1805RR5	DN1805RR5	1782mm	493mm	17mm	Right Door	Mild Steel
DN1806LR5	DN1806LR5	1782mm	593mm	17mm	Left Door	Mild Steel
DN1806R5	DN1806R5	1782mm	593mm	17mm	Plain	Mild Steel
DN1806RR5	DN1806RR5	1782mm	593mm	17mm	Right Door	Mild Steel
DN1808LR5	DN1808LR5	1782mm	793mm	17mm	Left Door	Mild Steel
DN1808R5	DN1808R5	1782mm	793mm	17mm	Plain	Mild Steel
DN1808RR5	DN1808RR5	1782mm	793mm	17mm	Right Door	Mild Steel
DN1810R5	DN1810R5	1782mm	993mm	17mm	Plain	Mild Steel
DN2004LR5	DN2004LR5	1982mm	393mm	17mm	Left Door	Mild Steel
DN2004RR5	DN2004RR5	1982mm	393mm	17mm	Right Door	Mild Steel
DN2005LR5	DN2005LR5	1982mm	493mm	17mm	Left Door	Mild Steel
DN2005R5	DN2005R5	1982mm	493mm	17mm	Plain	Mild Steel
DN2005RR5	DN2005RR5	1982mm	493mm	17mm	Right Door	Mild Steel
DN2006LR5	DN2006LR5	1982mm	593mm	17mm	Left Door	Mild Steel
DN2006R5	DN2006R5	1982mm	593mm	17mm	Plain	Mild Steel

Catalog Number	Article Number	Height	Width	Depth	Door Type	EnclosureMaterial
DN2006RR5	DN2006RR5	1982mm	593mm	17mm	Right Door	Mild Steel
DN2008LR5	DN2008LR5	1982mm	793mm	17mm	Left Door	Mild Steel
DN2008R5	DN2008R5	1982mm	793mm	17mm	Plain	Mild Steel
DN2008RR5	DN2008RR5	1982mm	793mm	17mm	Right Door	Mild Steel
DN2010R5	DN2010R5	1982mm	993mm	17mm	Plain	Mild Steel
DN2205LR5	DN2205LR5	2182mm	493mm	17mm	Left Door	Mild Steel
DN2205RR5	DN2205RR5	2182mm	493mm	17mm	Right Door	Mild Steel
DN2206LR5	DN2206LR5	2182mm	593mm	17mm	Left Door	Mild Steel
DN2206R5	DN2206R5	2182mm	593mm	17mm	Plain	Mild Steel
DN2206RR5	DN2206RR5	2182mm	593mm	17mm	Right Door	Mild Steel
DN2208R5	DN2208R5	2182mm	793mm	17mm	Plain	Mild Steel
DN1804R5		1782mm	393mm	17mm	Plain	Mild Steel
DN2004R5		1982mm	393mm	17mm	Plain	Mild Steel
DN2204R5		2182mm	393mm	17mm	Plain	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE