

Stainless Steel Glazed Doors, DNGS



Electrical components can be viewed while the transparent stainless steel door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

FEATURES

Description: Transparent door fitted with clear safety glass to view the inside of the enclosure. Equipped with double-bit 3 mm lock system and door frame. Allows all options of the locking programme.

Material: Frame: 2 mm AISI 304 stainless steel plate, AISI 316L (on request). Viewing area: 4 mm clear safety glass.

Finish: 400 pre-grained stainless steel.

Protection: IP 55, TYPE 12, 13, IK 07.

Mounting requirements: Use hinge kit DNMKS01 if not for replacement of standard door.

Pack quantity: 1 piece.

SPECIFICATIONS

Thickness: 2mm
Finish: Brushed
Material: Stainless Steel 304

Table 1/1

Catalog Number	Height	Width	Depth	Window Size	Enclosure Material	Product Family
DNGS1408	1400mm	800mm	17mm	1176 x 615mm	Mild Steel	Free-Standing
DNGS1606	1600mm	600mm	17mm	1376 x 415mm	Mild Steel	Free-Standing
DNGS1608	1600mm	800mm	17mm	1376 x 615mm	Mild Steel	Free-Standing
DNGS1610	1600mm	1000mm	17mm	1376 x 815mm	Mild Steel	Free-Standing
DNGS1806	1800mm	600mm	17mm	1576 x 415mm	Mild Steel	Free-Standing
DNGS1808	1800mm	800mm	17mm	1576 x 615mm	Mild Steel	Free-Standing
DNGS1810	1800mm	1000mm	17mm	1576 x 815mm	Mild Steel	Free-Standing
DNGS2006	2000mm	600mm	17mm	1776 x 415mm	Mild Steel	Free-Standing
DNGS2008	2000mm	800mm	17mm	1776 x 615mm	Mild Steel	Free-Standing
DNGS2010	2000mm	1000mm	17mm	1776 x 815mm	Mild Steel	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE