

# Top Cover With Cable Gland Opening, CRG



The roof plate with gland plate openings allow for easy cable entry in the field. Standard alternative solutions are available, which means that gland plates best suited for the application at hand can be used.

## FEATURES

Description: Roof plate with gland plates for cable entry.

Material: 1.5 mm steel plate.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 piece with gland plates, gaskets and mounting accessories.

Standard alternative solutions give customers the flexibility to use a gland plate that best suits the application, reducing labour time as machining is not required

The protection degree of the enclosure is maintained when the gland plate are mounted

Standard off the shelf wall mounted enclosure gland plates with different cabling options, are available as replacements

Roof plate with gland plates for cable entry

One piece with gland plates, gaskets and mounting accessories

SPECIFICATIONS

**Thickness:** 1.5mm  
**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

| Table 1/1      |        |       |       |                           |                           |                                |
|----------------|--------|-------|-------|---------------------------|---------------------------|--------------------------------|
| Catalog Number | Height | Width | Depth | Gland Plate Opening Width | Gland Plate Opening Depth | Number of Gland Plate Openings |
| CRG0808R5      | 17mm   | 800mm | 800mm | 210mm                     | 96mm                      | 2                              |
| CRG0806R5      | 17mm   | 800mm | 600mm | 210mm                     | 96mm                      | 2                              |
| CRG0608R5      | 17mm   | 600mm | 800mm | 310mm                     | 96mm                      | 1                              |
| CRG0606R5      | 17mm   | 600mm | 600mm | 310mm                     | 96mm                      | 1                              |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE