

EuropacPRO 19" Subrack Kit for DIN Connector, Retrofit Shielding

Power Utilities

Non-shielded subrack for Din Connector mounting EN 60603-2 (DIN 41612).



CERTIFICATIONS



FEATURES

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Aluminum construction

IP 20, in accordance with IEC 60529

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rails for connector mounting (IEC 60603-2 / DIN 41612)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-191	3 U	175 mm	1	DIN Connector	160 mm	Stainless Steel
24563-192	3 U	235 mm	1	DIN Connector	160 mm, 220 mm	Stainless Steel
24563-193	3 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Stainless Steel
24563-194	3 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Stainless Steel
24563-491	6 U	175 mm	1	DIN Connector	160 mm	Stainless Steel
24563-492	6 U	235 mm	1	DIN Connector	160 mm, 220 mm	Stainless Steel
24563-493	6 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Stainless Steel
24563-494	6 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Stainless Steel

Table 2/3

Catalog Number	Handle Included	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
24563-191	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-192	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-193	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-194	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-491	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-492	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-493	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

CatalogNumber	HandleIncluded	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
24563-494	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

Table 3/3

Catalog Number	Static Load
24563-191	11 kgf
24563-192	11 kgf
24563-193	11 kgf
24563-194	11 kgf
24563-491	11 kgf
24563-492	11 kgf
24563-493	11 kgf
24563-494	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE