

# Interscale Fan Holder With Fans

## Power Utilities

Interscale Fan Holder With Fans, for desktop cases and 19" chassis. Available in different sizes and with three fan versions, with a air flow volume from 10 to 170 m³/h.

### FEATURES

Fan holder for mounting on bottom of case

Fans are simple to fit to the fan holder using vibration-damping fixing material

Fan holders fix into desktop case with 2 plastic feet or into 19" case with 2 screws

Fan holder cannot be used in conjunction with the mounting plate (instead use mounting plate with integrated fan holder)

For technical data of fans, please see delivery includes

### SPECIFICATIONS

Table 1/3

| Catalog Number | Width | Depth | Package Quantity | Max Static Pressure | Max Ambient Temperature | Airflow |
|----------------|-------|-------|------------------|---------------------|-------------------------|---------|
| 24828-105      | 40 mm | 20 mm |                  |                     | 70 °C                   | 10 m³/h |
| 24828-107      | 40 mm | 20 mm |                  |                     | 70 °C                   | 10 m³/h |
| 24828-104      | 40 mm | 20 mm |                  |                     | 70 °C                   | 10 m³/h |
| 24828-205      | 80 mm | 25 mm |                  |                     | 70 °C                   | 19 m³/h |
| 24828-207      | 80 mm | 25 mm |                  |                     | 70 °C                   | 19 m³/h |
| 24828-204      | 80 mm | 25 mm |                  |                     | 70 °C                   | 19 m³/h |
| 24830-102      | 80 mm | 25 mm | 2                |                     |                         |         |

| CatalogNumber | Width  | Depth | Package Quantity | Max Static Pressure | Max Ambient Temperature | Airflow  |
|---------------|--------|-------|------------------|---------------------|-------------------------|----------|
| 24828-305     | 119 mm | 25 mm |                  |                     | 70 °C                   | 170 m³/h |
| 24828-307     | 119 mm | 25 mm |                  |                     | 70 °C                   | 170 m³/h |
| 24830-101     | 80 mm  | 25 mm |                  | 95.41 Pa            | 70 °C                   | 109 m³/h |

| Table 2/3      |             |        |                  |       |                |              |
|----------------|-------------|--------|------------------|-------|----------------|--------------|
| Catalog Number | Noise Level | Height | Input Voltage DC | Power | Product Family | Product Type |
| 24828-105      | 18 dB(A)    | 40 mm  | 12 V min         | 0.9 W | Interscale     | Fan Unit     |
| 24828-107      | 18 dB(A)    | 40 mm  | 12 V min         | 0.9 W | Interscale     | Fan Unit     |
| 24828-104      | 18 dB(A)    | 40 mm  | 12 V min         | 0.9 W | Interscale     | Fan Unit     |
| 24828-205      | 32 dB(A)    | 80 mm  | 12 V min         | 2 W   | Interscale     | Fan Unit     |
| 24828-207      | 32 dB(A)    | 80 mm  | 12 V min         | 2 W   | Interscale     | Fan Unit     |
| 24828-204      | 32 dB(A)    | 80 mm  | 12 V min         | 2 W   | Interscale     | Fan Unit     |
| 24830-102      |             | 80 mm  | 12 V min         |       |                | Fan Unit     |
| 24828-305      | 43 dB(A)    | 119 mm | 12 V min         | 5.3 W | Interscale     | Fan Unit     |
| 24828-307      | 43 dB(A)    | 119 mm | 12 V min         | 5.3 W | Interscale     | Fan Unit     |
| 24830-101      | 44.62 dB(A) | 80 mm  | 12 V min         |       |                | Fan Unit     |

| Table 3/3      |          |
|----------------|----------|
| Catalog Number | Type     |
| 24828-105      | Fan Tray |
| 24828-107      | Fan Tray |

| Catalog Number | Type     |
|----------------|----------|
| 24828-104      | Fan Tray |
| 24828-205      | Fan Tray |
| 24828-207      | Fan Tray |
| 24828-204      | Fan Tray |
| 24830-102      | Fan Tray |
| 24828-305      | Fan Tray |
| 24828-307      | Fan Tray |
| 24830-101      | Fan Tray |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE