

Varistar CP 19" Swing Frame Trim

Power Utilities

Varistar CP swing frame provides optimum space usage inside the rack. The swing frames come with handles.

FEATURES

Includes handle and cut-out for cable eyes

To cover the gap between swing frame and cabinet upright for 800 mm wide cabinets

Maximum swing bracket: 120 or 160

For swing frame with load-carrying capacity 150 kg, a stop is recommended for security reasons

Locking no. 333

Spare key for DIN semi-profile cylinder

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Color	Color Code	Material	Product Type	Protection Rating
21630-746	24 U	Black Grey	RAL 7021	Steel	Cabinet/Rack Frame	IP20
21630-749	24 U	Black Grey	RAL 7021	Steel	Cabinet/Rack Frame	IP20
21630-747	33 U	Black Grey	RAL 7021	Steel	Cabinet/Rack Frame	IP20
21630-750	33 U	Black Grey	RAL 7021	Steel	Cabinet/Rack Frame	IP20
21630-748	42 U	Black Grey	RAL 7021	Steel	Cabinet/Rack Frame	IP20
21630-751	42 U	Black Grey	RAL 7021	Steel	Cabinet/Rack Frame	IP20

Table 2/2

Catalog Number	Type	Works With
----------------	------	------------

21630-746	Swing	Varistar, Varistar CP
21630-749	Swing	Varistar, Varistar CP
21630-747	Swing	Varistar, Varistar CP
21630-750	Swing	Varistar, Varistar CP
21630-748	Swing	Varistar, Varistar CP
21630-751	Swing	Varistar, Varistar CP

ADDITIONAL PRODUCT DETAILS

Varistar CP swing frame provides optimum space usage inside the rack. The swing frames come with handles.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE