

Varistar CP Double Glazed Door, IP 20, 3-Point Locking

Power Utilities

FEATURES

Lever handle with key insert (2 keys)

Frame, St, 1.5 mm

Opening angle 180°

Security glass, 6 mm

Can be retrofitted with DIN profile half cylinder

Ingress protection class IP 20

Standard fitting, lock on right-hand door

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Height	Width	Color	Color Code	Locking Type
21630-686	24 U	1200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-687	24 U	1200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-688	29 U	1400 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-689	29 U	1400 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-690	33 U	1600 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-691	33 U	1600 mm	800 mm	Black Grey	RAL 7021	3-Point Locking

CatalogNumber	Rack Height	Height	Width	Color	Color Code	Locking Type
21630-692	38 U	1800 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-693	38 U	1800 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-694	42 U	2000 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-695	42 U	2000 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-696	47 U	2200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-697	47 U	2200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking

Table 2/2

Catalog Number	Product Type	Protection Rating	Type
21630-686	Cabinet Door	IP20	Glass Double Door
21630-687	Cabinet Door	IP20	Glass Double Door
21630-688	Cabinet Door	IP20	Glass Double Door
21630-689	Cabinet Door	IP20	Glass Double Door
21630-690	Cabinet Door	IP20	Glass Double Door
21630-691	Cabinet Door	IP20	Glass Double Door
21630-692	Cabinet Door	IP20	Glass Double Door
21630-693	Cabinet Door	IP20	Glass Double Door
21630-694	Cabinet Door	IP20	Glass Double Door
21630-695	Cabinet Door	IP20	Glass Double Door
21630-696	Cabinet Door	IP20	Glass Double Door

Catalog Number	Product Type	Protection Rating	Type
21630-697	Cabinet Door	IP20	Glass Double Door

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE