

# Varistar CP Plain Steel Door, Seismic IP55, With Multi-Point Locking

## Power Utilities

IP55 Seismic Steel Door with lever handle and multi-Point locking.

### FEATURES

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for EMC applications

### SPECIFICATIONS

Table 1/3

| Catalog Number | Rack Height | Height  | Width  | Color      | Color Code | Complies With                             |
|----------------|-------------|---------|--------|------------|------------|-------------------------------------------|
| 21630-752      | 33 U        | 1600 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 60529 |
| 21630-753      | 33 U        | 1600 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 60529 |
| 21630-754      | 38 U        | 600 mm  | 600 mm | Black Grey | RAL 7021   | IEC 61587-2,<br>IEC 61587-2,<br>IEC 60529 |
| 21630-755      | 38 U        | 1800 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 60529 |
| 21630-756      | 42 U        | 2000 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 60529 |
| 21630-757      | 42 U        | 2000 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 60529 |

| CatalogNumber | Rack Height | Height  | Width  | Color      | Color Code | Complies With                             |
|---------------|-------------|---------|--------|------------|------------|-------------------------------------------|
| 21630-758     | 47 U        | 2200 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 60529 |
| 21630-759     | 47 U        | 2200 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 60529 |

Table 2/3

| Catalog Number | Locking Type    | Material | Product Type | Protection Rating | Rack Width | Type              |
|----------------|-----------------|----------|--------------|-------------------|------------|-------------------|
| 21630-752      | 4-Point Locking | Steel    | Cabinet Door | IP55              |            | Steel Door, Plain |
| 21630-753      | 4-Point Locking | Steel    | Cabinet Door | IP55              | 800 HP     | Steel Door, Plain |
| 21630-754      | 4-Point Locking | Steel    | Cabinet Door | IP55              |            | Steel Door, Plain |
| 21630-755      | 4-Point Locking | Steel    | Cabinet Door | IP55              |            | Steel Door, Plain |
| 21630-756      | 4-Point Locking | Steel    | Cabinet Door | IP55              |            | Steel Door, Plain |
| 21630-757      | 4-Point Locking | Steel    | Cabinet Door | IP55              |            | Steel Door, Plain |
| 21630-758      | 5-Point Locking | Steel    | Cabinet Door | IP55              |            | Steel Door, Plain |
| 21630-759      | 5-Point Locking | Steel    | Cabinet Door | IP55              |            | Steel Door, Plain |

Table 3/3

| Catalog Number | Works With  |
|----------------|-------------|
| 21630-752      | Varistar CP |
| 21630-753      | Varistar CP |
| 21630-754      | Varistar CP |
| 21630-755      | Varistar CP |
| 21630-756      | Varistar CP |

| Catalog Number | Works With  |
|----------------|-------------|
| 21630-757      | Varistar CP |
| 21630-758      | Varistar CP |
| 21630-759      | Varistar CP |

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE