

HTV Self-Regulating Heating Cable



nVent RAYCHEM HTV self-regulating heating cable is designed for freeze protection or process temperature maintenance of pipes and vessels up to 205°C continuously, with a maximum exposure temperature of 260°C. The HTV cable has a solid construction with a high power retention (HPR) heating core and pressure extruded electrical insulation. It is then integrated with a robust metallic braid and a chemically resistant fluoropolymer outer jacket.

FEATURES

High power retention (HPR) heating core

Power retention: At least 95% after 10 years

Design life: 30 years or more depending on application

Simplified design in hazardous area: T3 and T2

Longer circuit lengths due to larger cross section conductors

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIONS

Max Maintain or Continuous Exposure Temperature, Power On:	205 °C
Max Intermittent Exposure Temperature, Power On/Off:	260 °C
Max Cumulative Hours for Intermittent Exposure:	2000 h
Ground Path Type:	Braid
Area Classification:	Non-Hazardous; Hazardous
Outer Jacket Material:	High Temperature Fluoropolymer

Table 1/1

Catalog Number	Supply Voltage	Nominal Power Output @ 10°C, 230V	Nominal Power Output @ 10°C, 120V
P000004312	90 – 130 V		9 W/m

Catalog Number	Supply Voltage	Nominal Power Output @ 10°C, 230V	Nominal Power Output @ 10°C, 120V
P000004313	90 – 130 V		16 W/m
P000004314	90 – 130 V		28 W/m
P000004315	90 – 130 V		32 W/m
P000004316	90 – 130 V		39 W/m
P000004317	90 – 130 V		49 W/m
P000004318	90 – 130 V		65 W/m
P000004319	190 – 277 V	9 W/m	
P000004320	190 – 277 V	16 W/m	
P000004321	190 – 277 V	25 W/m	
P000004322	190 – 277 V	32 W/m	
P000004323	190 – 277 V	38 W/m	
P000004324	190 – 277 V	48 W/m	
P000004325	190 – 277 V	64 W/m	
2000003152	190 – 277 V	90 W/m	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT