

SBS-R-FP Control Panel for Pipe Freeze Protection



SPECIFICATIONS

Phase Quantity:	3
IP Rating:	IP65
Protection:	Miniature- / Earth Leakage Circuit Breaker
Mounting:	Wall Mounted
Over Voltage Protection:	Yes

Table 1/2

Catalog Number	Item Name	Group Quantity	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30 mA
1244-016626	SBS-R-FP-1X16A	1	1	16 A, Type C	40 A	1
1244-016627	SBS-R-FP-3X16A	1	3	16 A, Type C	40 A	1
1244-016629	SBS-R-FP-1X10A	1	1	10 A, Type C	40 A	1
1244-016630	SBS-R-FP-3X10A	1	3	10 A, Type C	40 A	1
1244-016628	SBS-R-FP-6X16A	2	6	16 A, Type C	40 A	2
1244-016631	SBS-R-FP-6X10A	2	6	10 A, Type C	40 A	2

Table 2/2

Catalog Number	Item Name	Height	Width	Depth	Housing Material
1244-016626	SBS-R-FP-1X16A	286 mm	418 mm	148 mm	Plastic
1244-016627	SBS-R-FP-3X16A	436 mm	418 mm	148 mm	Plastic
1244-016629	SBS-R-FP-1X10A	246 mm	310 mm	148 mm	Plastic
1244-016630	SBS-R-FP-3X10A	436 mm	418 mm	148 mm	Plastic
1244-016628	SBS-R-FP-6X16A	586 mm	418 mm	148 mm	Plastic
1244-016631	SBS-R-FP-6X10A	586 mm	418 mm	148 mm	Plastic

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT