

EuropacPRO 19" Subrack Kit for Backplane, Slide Rail, Retrofit Shielding



Non-shielded subrack for backplane, subrack can be assembled on slide rails to support the subrack inside a cabinet.

CERTIFICATIONS



FEATURES

Subrack with side panel type F ("Flexible"), 19" bracket is depth-adjustable

Subrack can be used with slide rails

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 11 kg

Threaded insert, insulation strip pre-fitted

SPECIFICATIONS

Material:	Aluminum
Finish:	Anodized; Passivated
EMC Shielding:	No
Product Type:	Subrack/Chassis

Table 1/2

Catalog Number	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
----------------	-------------	-------	------------------	--------------	-------------	-----------------

24553-132	3U	235mm	1	Backplane	160mm, 220mm	Stainless Steel
24553-133	3U	295mm	1	Backplane	160mm, 220mm, 280mm	Stainless Steel
24553-134	3U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel
24553-432	6U	235mm	1	Backplane	160mm, 220mm	Stainless Steel
24553-433	6U	295mm	1	Backplane	160mm, 220mm, 280mm	Stainless Steel
24553-434	6U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel

Table 2/2

Catalog Number	Handle Included	Mounting	Complies With	Rack Width	Static Load	Quick Ship
24553-132	No	Rack	IEC 60297-3-103	84HP	11kg	No
24553-133	No	Rack	IEC 60297-3-103	84HP	11kg	No
24553-134	No	Rack	IEC 60297-3-103	84HP	11kg	No
24553-432	No	Rack	IEC 60297-3-103	84HP	11kg	No
24553-433	No	Rack	IEC 60297-3-103	84HP	11kg	No
24553-434	No	Rack	IEC 60297-3-103	84HP	11kg	No

ADDITIONAL PRODUCT DETAILS

Alternative product for older EuropacLab and Europac subrack series.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE