

EuropacPRO 19" Subrack Kit for DIN Connector, Slide Rail, Retrofit Shielding



Non-shielded subrack for Din Connector mounting EN 60603-2 , Subrack can be assembled on slide rails to support the subrack inside a cabinet.

CERTIFICATIONS



FEATURES

Subrack with side panel type F ("flexible"), 19" bracket with notch for slide rail assembly

Installed load up to 11 kg

Subrack can be used with slide rails

Horizontal rails, rear, for connector mounting (IEC 60603-2 / DIN 41612)

Threaded insert pre-fitted

SPECIFICATIONS

Static Load: 11kg
EMC Shielding: No
Product Type: Subrack/Chassis

Table 1/3

Catalog Number	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
----------------	-------------	-------	------------------	--------------	-------------	-----------------

24553-192	3U	235mm	1	DIN Connector	160mm, 220mm	Stainless Steel
24553-193	3U	295mm	1	DIN Connector	160mm, 220mm, 280mm	Stainless Steel
24553-194	3U	355mm	1	DIN Connector	160mm, 220mm, 280mm, 340mm	Stainless Steel
24553-492	6U	235mm	1	DIN Connector	160mm, 220mm	Stainless Steel
24553-493	6U	295mm	1	DIN Connector	160mm, 220mm, 280mm	Stainless Steel
24553-494	6U	355mm	1	DIN Connector	160mm, 220mm, 280mm, 340mm	Stainless Steel

Table 2/3

Catalog Number	Handle Included	Mounting	Complies With	Finish	Material	Rack Width
24553-192	No	Rack	IEC 60297-3-103	Anodized, Passivated	Aluminum	84HP
24553-193	No	Rack	IEC 60297-3-103	Anodized, Passivated		84HP
24553-194	No	Rack	IEC 60297-3-103	Anodized, Passivated		84HP
24553-492	No	Rack	IEC 60297-3-103	Anodized, Passivated		84HP
24553-493	No	Rack	IEC 60297-3-103	Anodized, Passivated		84HP
24553-494	No	Rack	IEC 60297-3-103	Anodized, Passivated		84HP

Table 3/3

Catalog Number	Quick Ship
24553-192	No
24553-193	No

Catalog Number	Quick Ship
24553-194	No
24553-492	No
24553-493	No
24553-494	No

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE