

Labrack 19" Open Rack Uprights



19" uprights for open or bare rack with up to 200 kg load capacity. These 19" uprights can be mounted on a mobile or stationary base.

CERTIFICATIONS



FEATURES

Mobile or stationary

Various shelves

Accessories for cable ducting

Stationary load-carrying capacity 200 kg or 150 kg (see specification table) at a defined center of gravity in the center of the lab rack

Recommended max. chassis depth 400 mm

SPECIFICATIONS

Width: 600mm

Product Type: Rack

Table 1/2

Catalog Number	Rack Height	Height	Frame Material	Package Quantity	Complies With	Finish
20118-742	39U	1831mm	Steel	1	IEC 60297-3-100	Powder Coated

CatalogNumber	Rack Height	Height	Frame Material	Package Quantity	Complies With	Finish
20118-741	24U	1164mm	Steel	1	IEC 60297-3-100	Powder Coated

Table 2/2

Catalog Number	Material	Static Load	Quick Ship
20118-742	Steel	150kg	No
20118-741	Steel	150kg	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE