

Novastar Cabinet With Glazed Door and Rear Panel



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

CERTIFICATIONS



FEATURES

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Bolted, die-cast frame with Al extrusions

With glass door (smoke grey) and rear panel

SPECIFICATIONS

Frame Material:	Aluminum
Material:	Aluminum; Steel
Product Type:	Cabinet
Complies With:	IEC 60529; IEC 60297-3-100
Protection Rating:	IP20

Table 1/3

Catalog Number	Rack Height	Frame Color	Height	Frame Color Code	Cladding Material	Width
15230-019	12U	Black Grey	589mm	RAL 7021	Steel	553mm
15230-020	16U	Black Grey	767mm	RAL 7021	Steel	553mm
15230-021	20U	Black Grey	945mm	RAL 7021	Steel	553mm
15230-022	38U	Black Grey	1745mm	RAL 7021	Steel	553mm
15230-023	38U	Black Grey	1745mm	RAL 7021	Steel	553mm
15230-024	43U	Black Grey	1967mm	RAL 7021	Steel	553mm
15230-025	43U	Black Grey	1967mm	RAL 7021	Steel	553mm
16230-019	12U	Black Grey	589mm	RAL 7021	Steel	553mm
16230-020	16U	Black Grey	767mm	RAL 7021	Steel	553mm
16230-021	20U	Black Grey	945mm	RAL 7021	Steel	553mm
16230-022	38U	Black Grey	1745mm	RAL 7021	Steel	553mm
16230-023	38U	Black Grey	1745mm	RAL 7021	Steel	553mm
16230-024	43U	Black Grey	1967mm	RAL 7021	Steel	553mm
16230-025	43U	Black Grey	1967mm	RAL 7021	Steel	553mm

Table 2/3

Catalog Number	Cladding Color	Depth	Static Load	Cladding Color Code	Package Quantity	Finish
15230-019	Black Grey	600mm	200kg	RAL 7021	1	Powder Coated
15230-020	Black Grey	600mm	200kg	RAL 7021	1	Powder Coated

CatalogNumber	Cladding Color	Depth	Static Load	Cladding Color Code	Package Quantity	Finish
15230-021	Black Grey	600mm	200kg	RAL 7021	1	Powder Coated
15230-022	Black Grey	600mm	400kg	RAL 7021	1	Powder Coated
15230-023	Black Grey	800mm	400kg	RAL 7021	1	Powder Coated
15230-024	Black Grey	600mm	400kg	RAL 7021	1	Powder Coated
15230-025	Black Grey	800mm	400kg	RAL 7021	1	Powder Coated
16230-019	Light Grey	600mm	200kg	RAL 7035	1	Powder Coated
16230-020	Light Grey	600mm	200kg	RAL 7035	1	Powder Coated
16230-021	Light Grey	600mm	200kg	RAL 7035	1	Powder Coated
16230-022	Light Grey	600mm	400kg	RAL 7035	1	Powder Coated
16230-023	Light Grey	800mm	400kg	RAL 7035	1	Powder Coated
16230-024	Light Grey	600mm	400kg	RAL 7035	1	Powder Coated
16230-025	Light Grey	800mm	400kg	RAL 7035	1	Powder Coated

Table 3/3

Catalog Number	Quick Ship
15230-019	No
15230-020	No
15230-021	No
15230-022	No
15230-023	No

Catalog Number	Quick Ship
15230-024	No
15230-025	No
16230-019	No
16230-020	No
16230-021	No
16230-022	No
16230-023	No
16230-024	No
16230-025	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE