

Socket Strip, IEC C13, With Wieland® Input



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



FEATURES

Input via Wieland® GST 18 plug

Installation height 1 U

In accordance with IEC 60320

Horizontal or vertical mounting

Output via IEC 60320 C-13 sockets

Socket strips can be rotated through all four directions (in 90° increments) during fitting

SPECIFICATIONS

Length:	438.5mm
Material:	Aluminum; Polyamide
Product Type:	Socket Strip

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-351	IEC C13	6	No	230V	Overcurrent Protection	1

CatalogNumber	Socket Type	SocketQuantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-350	IEC C13	6	No	230V	Overcurrent Protection	1
60110-340	IEC C13	12	No	230V		1
60110-349	IEC C13	6	No	230V	Overcurrent Protection	1
60110-342	IEC C13	12	No	230V		1
60110-341	IEC C13	12	No	230V		1

Table 2/2

Catalog Number	Color	Depth	Finish	Quick Ship
60110-351	Red	44mm	Anodized	No
60110-350	Black	44mm	Anodized	No
60110-340	Grey	44mm	Anodized	No
60110-349	Grey	44mm	Anodized	No
60110-342	Red	44mm	Anodized	No
60110-341	Black	44mm	Anodized	No

ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE