

Varistar Colocation Cabinet, RAL 7021



Colocation cabinets with 2, 3 or 4 divider units in RAL 7021 to accommodate servers while separating access and cabling of the compartments.

CERTIFICATIONS



FEATURES

Colocation cabinets with compartments

Flexible cabling, possible from above, below, left or right (data and power cables can be run separately)

Multi-point door latch

Perforated doors

Protection class IP 20

Color RAL 7021 (black grey)

SPECIFICATIONS

Product Type: Rack

Frame Material: Steel

Table 1/3

Catalog Number	Rack Height	Height	Cladding Material	Frame Color	Width	Frame Color Code
10130-202	40U	2000mm	Steel	Black Grey	600mm	RAL 7021

CatalogNumber	Rack Height	Height	Cladding Material	Frame Color	Width	Frame Color Code
10130-203	39U	2000mm	Steel	Black Grey	600mm	RAL 7021
10130-204	40U	2000mm	Steel	Black Grey	600mm	RAL 7021
10130-205	40U	2000mm	Steel	Black Grey	800mm	RAL 7021
10130-206	39U	2000mm	Steel	Black Grey	800mm	RAL 7021
10130-207	40U	2000mm	Steel	Black Grey	800mm	RAL 7021
10130-208	44U	2200mm	Steel	Black Grey	600mm	RAL 7021
10130-209	45U	2200mm	Steel	Black Grey	600mm	RAL 7021
10130-210	44U	2200mm	Steel	Black Grey	600mm	RAL 7021
10130-211	44U	2200mm	Steel	Black Grey	800mm	RAL 7021
10130-212	45U	2200mm	Steel	Black Grey	800mm	RAL 7021
10130-213	44U	2200mm	Steel	Black Grey	800mm	RAL 7021
10130-214	40U	2000mm	Steel	Black Grey	600mm	RAL 7021
10130-215	39U	2000mm	Steel	Black Grey	600mm	RAL 7021
10130-216	40U	2000mm	Steel	Black Grey	600mm	RAL 7021
10130-217	40U	2000mm	Steel	Black Grey	800mm	RAL 7021
10130-218	39U	2000mm	Steel	Black Grey	800mm	RAL 7021
10130-219	40U	2000mm	Steel	Black Grey	800mm	RAL 7021
10130-220	44U	2200mm	Steel	Black Grey	600mm	RAL 7021

CatalogNumber	Rack Height	Height	Cladding Material	Frame Color	Width	Frame Color Code
10130-221	45U	2200mm	Steel	Black Grey	600mm	RAL 7021
10130-222	44U	2200mm	Steel	Black Grey	600mm	RAL 7021
10130-223	44U	2200mm	Steel	Black Grey	800mm	RAL 7021
10130-224	45U	2200mm	Steel	Black Grey	800mm	RAL 7021
10130-225	44U	2200mm	Steel	Black Grey	800mm	RAL 7021
10130-257	45U	2450mm	Steel	Black Grey	600mm	RAL 7021
10130-258	48U	2450mm	Steel	Black Grey	600mm	RAL 7021
10130-259	48U	2450mm	Steel	Black Grey	600mm	RAL 7021
10130-260	45U	2450mm	Steel	Black Grey	800mm	RAL 7021
10130-261	48U	2450mm	Steel	Black Grey	800mm	RAL 7021
10130-262	48U	2450mm	Steel	Black Grey	800mm	RAL 7021
10130-269	45U	2450mm	Steel	Black Grey	600mm	RAL 7021
10130-270	48U	2450mm	Steel	Black Grey	600mm	RAL 7021
10130-271	48U	2450mm	Steel	Black Grey	600mm	RAL 7021
10130-272	45U	2450mm	Steel	Black Grey	800mm	RAL 7021
10130-273	48U	2450mm	Steel	Black Grey	800mm	RAL 7021
10130-274	48U	2450mm	Steel	Black Grey	800mm	RAL 7021

Table 2/3

Catalog Number	Cladding Color	Cladding Color Code	Depth	Package Quantity	Number of Compartments	Finish
10130-202	Black Grey	RAL 7021	1000mm	1	2	Powder Coated
10130-203	Black Grey	RAL 7021	1000mm	1	3	Powder Coated
10130-204	Black Grey	RAL 7021	1000mm	1	4	Powder Coated
10130-205	Black Grey	RAL 7021	1000mm	1	2	Powder Coated
10130-206	Black Grey	RAL 7021	1000mm	1	3	Powder Coated
10130-207	Black Grey	RAL 7021	1000mm	1	4	Powder Coated
10130-208	Black Grey	RAL 7021	1000mm	1	2	Powder Coated
10130-209	Black Grey	RAL 7021	1000mm	1	3	Powder Coated
10130-210	Black Grey	RAL 7021	1000mm	1	4	Powder Coated
10130-211	Black Grey	RAL 7021	1000mm	1	2	Powder Coated
10130-212	Black Grey	RAL 7021	1000mm	1	3	Powder Coated
10130-213	Black Grey	RAL 7021	1000mm	1	4	Powder Coated
10130-214	Black Grey	RAL 7021	1200mm	1	2	Powder Coated
10130-215	Black Grey	RAL 7021	1200mm	1	3	Powder Coated
10130-216	Black Grey	RAL 7021	1200mm	1	4	Powder Coated
10130-217	Black Grey	RAL 7021	1200mm	1	2	Powder Coated
10130-218	Black Grey	RAL 7021	1200mm	1	3	Powder Coated
10130-219	Black Grey	RAL 7021	1200mm	1	4	Powder Coated

CatalogNumber	Cladding Color	Cladding Color Code	Depth	Package Quantity	Number of Compartments	Finish
10130-220	Black Grey	RAL 7021	1200mm	1	2	Powder Coated
10130-221	Black Grey	RAL 7021	1200mm	1	3	Powder Coated
10130-222	Black Grey	RAL 7021	1200mm	1	4	Powder Coated
10130-223	Black Grey	RAL 7021	1200mm	1	2	Powder Coated
10130-224	Black Grey	RAL 7021	1200mm	1	3	Powder Coated
10130-225	Black Grey	RAL 7021	1200mm	1	4	Powder Coated
10130-257	Black Grey	RAL 7021	1000mm	1	2	Powder Coated
10130-258	Black Grey	RAL 7021	1000mm	1	3	Powder Coated
10130-259	Black Grey	RAL 7021	1000mm	1	4	Powder Coated
10130-260	Black Grey	RAL 7021	1000mm	1	2	Powder Coated
10130-261	Black Grey	RAL 7021	1000mm	1	3	Powder Coated
10130-262	Black Grey	RAL 7021	1000mm	1	4	Powder Coated
10130-269	Black Grey	RAL 7021	1200mm	1	2	Powder Coated
10130-270	Black Grey	RAL 7021	1200mm	1	3	Powder Coated
10130-271	Black Grey	RAL 7021	1200mm	1	4	Powder Coated
10130-272	Black Grey	RAL 7021	1200mm	1	2	Powder Coated
10130-273	Black Grey	RAL 7021	1200mm	1	3	Powder Coated
10130-274	Black Grey	RAL 7021	1200mm	1	4	Powder Coated

Table 3/3

Catalog Number	Material	Static Load	Quick Ship
10130-202	Steel	800kg	No
10130-203	Steel	800kg	No
10130-204	Steel	800kg	No
10130-205	Steel	800kg	No
10130-206	Steel	800kg	No
10130-207	Steel	800kg	No
10130-208	Steel	800kg	No
10130-209	Steel	800kg	No
10130-210	Steel	800kg	No
10130-211	Steel	800kg	No
10130-212	Steel	800kg	No
10130-213	Steel	800kg	No
10130-214	Steel	800kg	No
10130-215	Steel	800kg	No
10130-216	Steel	800kg	No
10130-217	Steel	800kg	No
10130-218	Steel	800kg	No
10130-219	Steel	800kg	No

Catalog Number	Material	Static Load	Quick Ship
10130-220	Steel	800kg	No
10130-221	Steel	800kg	No
10130-222	Steel	800kg	No
10130-223	Steel	800kg	No
10130-224	Steel	800kg	No
10130-225	Steel	800kg	No
10130-257	Steel	800kg	No
10130-258	Steel	800kg	No
10130-259	Steel	800kg	No
10130-260	Steel	800kg	No
10130-261	Steel	800kg	No
10130-262	Steel	800kg	No
10130-269	Steel	800kg	No
10130-270	Steel	800kg	No
10130-271	Steel	800kg	No
10130-272	Steel	800kg	No
10130-273	Steel	800kg	No
10130-274	Steel	800kg	No

ADDITIONAL PRODUCT DETAILS

Side panel must be ordered separately. For suitable cable panel see Accessories.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE