

Varistar Colocation Cabinet, RAL 7035



Colocation cabinets with 2, 3 or 4 divider units in RAL 7035 to accommodate servers while separating access and cabling of the compartments.

CERTIFICATIONS



FEATURES

Colocation cabinets with compartments to accommodate e.g. servers

Flexible cabling, possible from above, below, left or right (data and power cables can be run separately)

Multi-point door locking

Perforated doors

Protection class IP 20

Color RAL 7035

SPECIFICATIONS

Product Type: Rack

Frame Material: Steel

Table 1/3

Catalog Number	Rack Height	Height	Cladding Material	Frame Color	Width	Frame Color Code
11130-202	40U	2000mm	Steel	Light Grey	600mm	RAL 7021

CatalogNumber	Rack Height	Height	Cladding Material	Frame Color	Width	Frame Color Code
11130-203	39U	2000mm	Steel	Light Grey	600mm	RAL 7021
11130-204	40U	2000mm	Steel	Light Grey	600mm	RAL 7021
11130-205	40U	2000mm	Steel	Light Grey	800mm	RAL 7021
11130-206	39U	2000mm	Steel	Light Grey	800mm	RAL 7035
11130-207	40U	2000mm	Steel	Light Grey	800mm	RAL 7021
11130-208	44U	2200mm	Steel	Light Grey	600mm	RAL 7021
11130-209	45U	2200mm	Steel	Light Grey	600mm	RAL 7021
11130-210	44U	2200mm	Steel	Light Grey	600mm	RAL 7021
11130-211	44U	2200mm	Steel	Light Grey	800mm	RAL 7021
11130-212	45U	2200mm	Steel	Black Grey	800mm	RAL 7021
11130-213	44U	2200mm	Steel	Light Grey	800mm	RAL 7021
11130-214	40U	2000mm	Steel	Light Grey	600mm	RAL 7021
11130-215	39U	2000mm	Steel	Light Grey	600mm	RAL 7021
11130-216	40U	2000mm	Steel	Light Grey	600mm	RAL 7021
11130-217	40U	2000mm	Steel	Light Grey	800mm	RAL 7021
11130-218	39U	2000mm	Steel	Black Grey	800mm	RAL 7021
11130-219	40U	2000mm	Steel	Light Grey	800mm	RAL 7021
11130-220	44U	2200mm	Steel	Light Grey	600mm	RAL 7021

CatalogNumber	Rack Height	Height	Cladding Material	Frame Color	Width	Frame Color Code
11130-221	45U	2200mm	Steel	Light Grey	600mm	RAL 7021
11130-222	44U	2200mm	Steel	Light Grey	600mm	RAL 7021
11130-223	44U	2200mm	Steel	Light Grey	800mm	RAL 7021
11130-224	45U	2200mm	Steel	Light Grey	800mm	RAL 7021
11130-225	44U	2200mm	Steel	Light Grey	800mm	RAL 7021
11130-257	45U	2450mm	Steel	Light Grey	600mm	RAL 7021
11130-258	48U	2450mm	Steel	Light Grey	600mm	RAL 7021
11130-259	48U	2450mm	Steel	Light Grey	600mm	RAL 7021
11130-260	45U	2450mm	Steel	Light Grey	800mm	RAL 7021
11130-261	48U	2450mm	Steel	Light Grey	800mm	RAL 7021
11130-262	48U	2450mm	Steel	Light Grey	800mm	RAL 7021
11130-269	45U	2450mm	Steel	Light Grey	600mm	RAL 7021
11130-270	48U	2450mm	Steel	Light Grey	600mm	RAL 7021
11130-271	48U	2450mm	Steel	Light Grey	600mm	RAL 7021
11130-272	45U	2450mm	Steel	Light Grey	800mm	RAL 7021
11130-273	48U	2450mm	Steel	Light Grey	800mm	RAL 7021
11130-274	48U	2450mm	Steel	Light Grey	800mm	RAL 7021

Table 2/3

Catalog Number	Cladding Color	Cladding Color Code	Depth	Package Quantity	Number of Compartments	Finish
11130-202	Light Grey	RAL 7035	1000mm	1	2	Powder Coated
11130-203	Light Grey	RAL 7035	1000mm	1	3	Powder Coated
11130-204	Light Grey	RAL 7035	1000mm	1	4	Powder Coated
11130-205	Light Grey	RAL 7035	1000mm	1	2	Powder Coated
11130-206	Light Grey	RAL 7035	1000mm	1	3	Powder Coated
11130-207	Light Grey	RAL 7035	1000mm	1	4	Powder Coated
11130-208	Light Grey	RAL 7035	1000mm	1	2	Powder Coated
11130-209	Light Grey	RAL 7035	1000mm	1	3	Powder Coated
11130-210	Light Grey	RAL 7035	1000mm	1	4	Powder Coated
11130-211	Light Grey	RAL 7035	1000mm	1	2	Powder Coated
11130-212	Light Grey	RAL 7035	1000mm	1	3	Powder Coated
11130-213	Light Grey	RAL 7035	1000mm	1	4	Powder Coated
11130-214	Light Grey	RAL 7035	1200mm	1	2	Powder Coated
11130-215	Light Grey	RAL 7035	1200mm	1	3	Powder Coated
11130-216	Light Grey	RAL 7035	1200mm	1	4	Powder Coated
11130-217	Light Grey	RAL 7035	1200mm	1	2	Powder Coated
11130-218	Light Grey	RAL 7035	1200mm	1	3	Powder Coated
11130-219	Light Grey	RAL 7035	1200mm	1	4	Powder Coated

CatalogNumber	Cladding Color	Cladding Color Code	Depth	Package Quantity	Number of Compartments	Finish
11130-220	Light Grey	RAL 7035	1200mm	1	2	Powder Coated
11130-221	Light Grey	RAL 7035	1200mm	1	3	Powder Coated
11130-222	Light Grey	RAL 7035	1200mm	1	4	Powder Coated
11130-223	Light Grey	RAL 7035	1200mm	1	2	Powder Coated
11130-224	Light Grey	RAL 7035	1200mm	1	3	Powder Coated
11130-225	Light Grey	RAL 7035	1200mm	1	4	Powder Coated
11130-257	Light Grey	RAL 7035	1000mm	1	2	Powder Coated
11130-258	Light Grey	RAL 7035	1000mm	1	3	Powder Coated
11130-259	Light Grey	RAL 7035	1000mm	1	4	Powder Coated
11130-260	Light Grey	RAL 7035	1000mm	1	2	Powder Coated
11130-261	Light Grey	RAL 7035	1000mm	1	3	Powder Coated
11130-262	Light Grey	RAL 7035	1000mm	1	4	Powder Coated
11130-269	Light Grey	RAL 7035	1200mm	1	2	Powder Coated
11130-270	Light Grey	RAL 7035	1200mm	1	3	Powder Coated
11130-271	Light Grey	RAL 7035	1200mm	1	4	Powder Coated
11130-272	Light Grey	RAL 7035	1200mm	1	2	Powder Coated
11130-273	Light Grey	RAL 7035	1200mm	1	3	Powder Coated
11130-274	Light Grey	RAL 7035	1200mm	1	4	Powder Coated

Table 3/3

Catalog Number	Material	Static Load	Quick Ship
11130-202	Steel	800kg	No
11130-203	Steel	800kg	No
11130-204	Steel	800kg	No
11130-205	Steel	800kg	No
11130-206	Steel	800kg	No
11130-207	Steel	800kg	No
11130-208	Steel	800kg	No
11130-209	Steel	800kg	No
11130-210	Steel	800kg	No
11130-211	Steel	800kg	No
11130-212	Steel	800kg	No
11130-213	Steel	800kg	No
11130-214	Steel	800kg	No
11130-215	Steel	800kg	No
11130-216	Steel	800kg	No
11130-217	Steel	800kg	No
11130-218	Steel	800kg	No
11130-219	Steel	800kg	No

Catalog Number	Material	Static Load	Quick Ship
11130-220	Steel	800kg	No
11130-221	Steel	800kg	No
11130-222	Steel	800kg	No
11130-223	Steel	800kg	No
11130-224	Steel	800kg	No
11130-225	Steel	800kg	No
11130-257	Steel	800kg	No
11130-258	Steel	800kg	No
11130-259	Steel	800kg	No
11130-260	Steel	800kg	No
11130-261	Steel	800kg	No
11130-262	Steel	800kg	No
11130-269	Steel	800kg	No
11130-270	Steel	800kg	No
11130-271	Steel	800kg	No
11130-272	Steel	800kg	No
11130-273	Steel	800kg	No
11130-274	Steel	800kg	No

ADDITIONAL PRODUCT DETAILS

Side panel must be ordered separately. For suitable cable panel see Accessories.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE