

Bolt Close Conduit/Pipe Clamp



CERTIFICATIONS



FEATURES

Retained bolt and built-in nut means there are less parts to handle or drop

Combo head bolt works with slotted, hex, #3 phillips or #2 robertson drivers

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Nut Type	Outer Diameter (OD)	Hole Size (HS)
CD2.5BSS		Stainless Steel 304 (EN 1.4301)		Hex Nut	31 - 38 mm	6.75 mm
CD2BSS		Stainless Steel 304 (EN 1.4301)		Hex Nut	25 - 33 mm	6.75 mm
CD3BSS		Stainless Steel 304 (EN 1.4301)		Hex Nut	36 - 43 mm	6.75 mm
CD0B	181140	Steel	Electrogalvanized	Built-In Nut	17 - 22 mm	7.14 mm

CatalogNumber	Article Number	Material	Finish	Nut Type	Outer Diameter (OD)	Hole Size (HS)
CD0BSS		Stainless Steel 304 (EN 1.4301)		Hex Nut	17 - 22 mm	7.14 mm
CD1B	181190	Steel	Electrogalvanized	Built-In Nut	19 - 25 mm	7.14 mm
CD1BSS		Stainless Steel 304 (EN 1.4301)		Hex Nut	19 - 25 mm	7.14 mm
CD2.5B	181370	Steel	Electrogalvanized	Built-In Nut	31 - 38 mm	7.14 mm
CD2B	181150	Steel	Electrogalvanized	Built-In Nut	25 - 33 mm	7.14 mm
CD3B	181380	Steel	Electrogalvanized	Built-In Nut	36 - 43 mm	7.14 mm
CD4B	181390	Steel	Electrogalvanized	Built-In Nut	45 - 48 mm	7.14 mm
CD4BSS		Stainless Steel 304 (EN 1.4301)		Hex Nut	45 - 48 mm	7.14 mm
CD5B	181470	Steel	Electrogalvanized	Built-In Nut	49 - 73 mm	7.14 mm
CD5BSS		Stainless Steel 304 (EN 1.4301)		Hex Nut	49 - 73 mm	7.14 mm
CD6B	181480	Steel	Electrogalvanized	Hex Nut	66 - 76 mm	7.9 mm
CD7B	181490	Steel	Electrogalvanized	Hex Nut	80 - 90 mm	7.9 mm
CD8B	181500	Steel	Electrogalvanized	Hex Nut	95 - 105 mm	7.9 mm
CD9B	181540	Steel	Electrogalvanized	Hex Nut	108 - 115 mm	7.9 mm
CD6BSS		Stainless Steel 304 (EN 1.4301)		Hex Nut	66 - 76 mm	8.33 mm
CD7BSS		Stainless Steel 304 (EN 1.4301)		Hex Nut	80 - 90 mm	8.33 mm


CatalogNumber	Article Number	Material	Finish	Nut Type	Outer Diameter (OD)	Hole Size (HS)
CD8BSS		Stainless Steel 304 (EN 1.4301)		Hex Nut	95 - 105 mm	8.33 mm
CD9BSS		Stainless Steel 304 (EN 1.4301)		Hex Nut	108 - 115 mm	8.33 mm
CD1B37		Steel	Electrogalvanized	Built-In Nut	19 - 25 mm	10.32 mm
CD2B37		Steel	Electrogalvanized	Built-In Nut	25 - 33 mm	10.32 mm

Table 2/2

Catalog Number	Article Number	Static Load 1 (F1)	Static Load 2 (F2)	Certifications
CD2.5BSS		880N	220N	UL, cUL
CD2BSS		880N	220N	
CD3BSS		880N	220N	UL, cUL
CD0B	181140	880N	220N	UL, cUL
CD0BSS		880N	220N	UL, cUL
CD1B	181190	880N	220N	cUL, ITB, UL
CD1BSS		880N	220N	UL, cUL
CD2.5B	181370	880N	220N	cUL, UL
CD2B	181150	880N	220N	cUL, UL
CD3B	181380	880N	220N	UL, cUL, ITB
CD4B	181390	880N	220N	cUL, ITB, UL
CD4BSS		880N	220N	UL, cUL

Catalog Number	Article Number	Static Load 1 (F1)	Static Load 2 (F2)	Certifications
CD5B	181470	880N	220N	cUL, UL, ITB
CD5BSS		1550N	220N	cUL, UL
CD6B	181480	1550N	220N	
CD7B	181490	1550N	220N	
CD8B	181500	1550N	220N	
CD9B	181540	1550N	220N	
CD6BSS		1550N	220N	
CD7BSS		1550N	220N	
CD8BSS		1550N	220N	
CD9BSS		1550N	220N	
CD1B37		880N	220N	
CD2B37		880N	220N	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

