

Joint Bond T9 Complete Welder Pair, Power

Data Solutions



FEATURES

Complete welder assembly provides a convenient means of attaching jumper bonds to the head of the rail

Connection is made within the confines of the splice plate

Includes mold cleaner and flint ignitor

SPECIFICATIONS

Rail Type:	85 lb to 141 lb T-Rail Sections
Bond Terminal Style:	C
Material:	Graphite; Steel; Thermoplastic

Table 1/1

Catalog Number	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
PBCT92J	2/0 Ropelay	12.19mm	T9
PBCT9S5	2/0 Composite	13.36mm	T9
PBCT9S6	3/0 Composite	14.53mm	T9
PBCT92S	4/0 Ropelay	15.49mm	T9

Catalog Number	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
PBCT92W	250 kcmil Ropelay	19.05mm	T9
PBXLCT92W	250 kcmil Ropelay	19.05mm	T9

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE