

LHX+ Air/Liquid Heat Exchanger 115 V UL

Data Solutions



FEATURES

19" mountable Air/liquid heat exchanger with fan

Easy replaceable fans without dismounting the heat exchanger

Coolant feed from top or bottom

UL Certified

SPECIFICATIONS

Depth: 500mm

Product Type: Air/Liquid Heat Exchanger

Table 1/2

Catalog Number	Package Quantity	Supply Voltage	Redundant Power Supply	Coolant Feed	Height	Width
29714-022	1	115V min	No	Bottom	266mm	426mm
29714-027	1	115V min	No	Bottom	266mm	426mm
29714-033	1	115V min	No	Bottom	266mm	426mm
29714-036	1	115V min	No	Bottom	266mm	426mm

Table 2/2

Catalog Number	Works With
29714-022	Varistar, Varistar CP
29714-027	Varistar, Varistar CP
29714-033	Varistar, Varistar CP
29714-036	Varistar, Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order separatly: Monitoring via Control unit, water control package, display and door contact switch.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE