

Varistar Colocation Cabinet, RAL 9003

Data Solutions



Colocation cabinets with 2, 3 or 4 divider units in RAL 9003 to accommodate servers while separating access and cabling of the compartments.

CERTIFICATIONS



FEATURES

Colocation cabinets with compartments to accommodate e.g. servers

Flexible cabling, possible from above, below, left or right (data and power cables can be run separately)

Multi-point door locking

Perforated doors

Protection class IP 20

Color RAL 9003

SPECIFICATIONS

Product Type: Rack

Frame Material: Steel

Table 1/3

Catalog Number	Rack Height	Height	Cladding Material	Frame Color	Width	Frame Color Code
----------------	-------------	--------	-------------------	-------------	-------	------------------

12130-202	40U	2000mm	Steel	Signal White	600mm	RAL 7021
12130-203	39U	2000mm	Steel	Signal White	600mm	RAL 7021
12130-204	40U	2000mm	Steel	Signal White	600mm	RAL 7021
12130-205	40U	2000mm	Steel	Signal White	800mm	RAL 7021
12130-206	39U	2000mm	Steel	Black Grey	800mm	RAL 7021
12130-207	40U	2000mm	Steel	Signal White	800mm	RAL 7021
12130-208	44U	2200mm	Steel	Signal White	600mm	RAL 7021
12130-209	45U	2200mm	Steel	Signal White	600mm	RAL 7021
12130-210	44U	2200mm	Steel	Signal White	600mm	RAL 7021
12130-211	44U	2200mm	Steel	Signal White	800mm	RAL 7021
12130-212	45U	2200mm	Steel	Black Grey	800mm	RAL 7021
12130-213	44U	2200mm	Steel	Signal White	800mm	RAL 7021
12130-214	40U	2000mm	Steel	Signal White	600mm	RAL 7021
12130-215	39U	2000mm	Steel	Signal White	600mm	RAL 7021
12130-216	40U	2000mm	Steel	Signal White	600mm	RAL 7021
12130-217	40U	2000mm	Steel	Signal White	800mm	RAL 7021
12130-218	39U	2000mm	Steel	Black Grey	800mm	RAL 7021
12130-219	40U	2000mm	Steel	Signal White	800mm	RAL 7021
12130-220	44U	2200mm	Steel	Signal White	600mm	RAL 7021

12130-221	45U	2200mm	Steel	Signal White	600mm	RAL 7021
12130-222	44U	2200mm	Steel	Signal White	600mm	RAL 7021
12130-223	44U	2200mm	Steel	Signal White	800mm	RAL 7021
12130-224	45U	2200mm	Steel	Signal White	800mm	RAL 7021
12130-225	44U	2200mm	Steel	Signal White	800mm	RAL 7021
12130-257	45U	2450mm	Steel	Signal White	600mm	RAL 7021
12130-258	48U	2450mm	Steel	Signal White	600mm	RAL 7021
12130-259	48U	2450mm	Steel	Signal White	600mm	RAL 7021
12130-260	45U	2450mm	Steel	Signal White	800mm	RAL 7021
12130-261	48U	2450mm	Steel	Signal White	800mm	RAL 7021
12130-262	48U	2450mm	Steel	Signal White	800mm	RAL 7021
12130-269	45U	2450mm	Steel	Signal White	600mm	RAL 7021
12130-270	48U	2450mm	Steel	Signal White	600mm	RAL 7021
12130-271	48U	2450mm	Steel	Signal White	600mm	RAL 7021
12130-272	45U	2450mm	Steel	Signal White	800mm	RAL 7021
12130-273	48U	2450mm	Steel	Signal White	800mm	RAL 7021
12130-274	48U	2450mm	Steel	Signal White	800mm	RAL 7021

Table 2/3

Catalog Number	Cladding Color	Cladding Color Code	Depth	Package Quantity	Number of Compartments	Finish
----------------	----------------	---------------------	-------	------------------	------------------------	--------

12130-202	Signal White	RAL 9003	1000mm	1	2	Powder Coated
12130-203	Signal White	RAL 9003	1000mm	1	3	Powder Coated
12130-204	Signal White	RAL 9003	1000mm	1	4	Powder Coated
12130-205	Signal White	RAL 9003	1000mm	1	2	Powder Coated
12130-206	Signal White	RAL 9003	1000mm	1	3	Powder Coated
12130-207	Signal White	RAL 9003	1000mm	1	4	Powder Coated
12130-208	Signal White	RAL 9003	1000mm	1	2	Powder Coated
12130-209	Signal White	RAL 9003	1000mm	1	3	Powder Coated
12130-210	Signal White	RAL 9003	1000mm	1	4	Powder Coated
12130-211	Signal White	RAL 9003	1000mm	1	2	Powder Coated
12130-212	Signal White	RAL 9003	1000mm	1	3	Powder Coated
12130-213	Signal White	RAL 9003	1000mm	1	4	Powder Coated
12130-214	Signal White	RAL 9003	1200mm	1	2	Powder Coated
12130-215	Signal White	RAL 9003	1200mm	1	3	Powder Coated
12130-216	Signal White	RAL 9003	1200mm	1	4	Powder Coated
12130-217	Signal White	RAL 9003	1200mm	1	2	Powder Coated
12130-218	Signal White	RAL 9003	1200mm	1	3	Powder Coated
12130-219	Signal White	RAL 9003	1200mm	1	4	Powder Coated
12130-220	Signal White	RAL 9003	1200mm	1	2	Powder Coated

12130-221	Signal White	RAL 9003	1200mm	1	3	Powder Coated
12130-222	Signal White	RAL 9003	1200mm	1	4	Powder Coated
12130-223	Signal White	RAL 9003	1200mm	1	2	Powder Coated
12130-224	Signal White	RAL 9003	1200mm	1	3	Powder Coated
12130-225	Signal White	RAL 9003	1200mm	1	4	Powder Coated
12130-257	Signal White	RAL 9003	1000mm	1	2	Powder Coated
12130-258	Signal White	RAL 9003	1000mm	1	3	Powder Coated
12130-259	Signal White	RAL 9003	1000mm	1	4	Powder Coated
12130-260	Signal White	RAL 9003	1000mm	1	2	Powder Coated
12130-261	Signal White	RAL 9003	1000mm	1	3	Powder Coated
12130-262	Signal White	RAL 9003	1000mm	1	4	Powder Coated
12130-269	Signal White	RAL 9003	1200mm	1	2	Powder Coated
12130-270	Signal White	RAL 9003	1200mm	1	3	Powder Coated
12130-271	Signal White	RAL 9003	1200mm	1	4	Powder Coated
12130-272	Signal White	RAL 9003	1200mm	1	2	Powder Coated
12130-273	Signal White	RAL 9003	1200mm	1	3	Powder Coated
12130-274	Signal White	RAL 9003	1200mm	1	4	Powder Coated

Table 3/3

Catalog Number	Material	Static Load
12130-202	Steel	800kg

Catalog Number	Material	Static Load
12130-203	Steel	800kg
12130-204	Steel	800kg
12130-205	Steel	800kg
12130-206	Steel	800kg
12130-207	Steel	800kg
12130-208	Steel	800kg
12130-209	Steel	800kg
12130-210	Steel	800kg
12130-211	Steel	800kg
12130-212	Steel	800kg
12130-213	Steel	800kg
12130-214	Steel	800kg
12130-215	Steel	800kg
12130-216	Steel	800kg
12130-217	Steel	800kg
12130-218	Steel	800kg
12130-219	Steel	800kg
12130-220	Steel	800kg

Catalog Number	Material	Static Load
12130-221	Steel	800kg
12130-222	Steel	800kg
12130-223	Steel	800kg
12130-224	Steel	800kg
12130-225	Steel	800kg
12130-257	Steel	800kg
12130-258	Steel	800kg
12130-259	Steel	800kg
12130-260	Steel	800kg
12130-261	Steel	800kg
12130-262	Steel	800kg
12130-269	Steel	800kg
12130-270	Steel	800kg
12130-271	Steel	800kg
12130-272	Steel	800kg
12130-273	Steel	800kg
12130-274	Steel	800kg

ADDITIONAL PRODUCT DETAILS

Side panel must be ordered separately. For suitable cable panel see Accessories.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE