

Varistar CP Glazed Door With 3-Point Locking

Data Solutions



Glazed door with 3 point locking allows stronger contact between door and the cabinet frame.

FEATURES

Glazed Door With 3-Point Locking, With Lock

Lever handle with key insert (2 keys)

Opening angle 180°

Security glass, 6 mm

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIONS

Locking Type: 3-Point Locking

Product Type: Cabinet Door

Material: Steel; Glass

Table 1/2

Catalog Number	Rack Height	Height	Width	Protection Rating	Package Quantity	Color
21630-095	42U	2000mm	800mm	IP20	1	Black Grey
21630-093	47U	2200mm	600mm	IP20	1	Black Grey

CatalogNumber	Rack Height	Height	Width	Protection Rating	Package Quantity	Color
21630-725	42U	2000mm	600mm	IP55	1	Black Grey
21630-420	33U	1600mm	600mm	IP20	1	Black Grey
21630-417	24U	1200mm	800mm	IP20	1	Black Grey
21630-724	38U	1800mm	800mm	IP55	1	Black Grey
21630-094	52U	2450mm	600mm	IP20	1	Black Grey
21630-723	38U	1800mm	600mm	IP55	1	Black Grey
21630-421	33U	1600mm	800mm	IP20	1	Black Grey
21630-722	33U	1600mm	800mm	IP55	1	Black Grey
21630-422	38U	1800mm	600mm	IP20	1	Black Grey
21630-418	29U	1400mm	600mm	IP20	1	Black Grey
21630-721	33U	1600mm	600mm	IP55	1	Black Grey
21630-416	24U	1200mm	600mm	IP20	1	Black Grey
21630-720	29U	1400mm	800mm	IP55	1	Black Grey
21630-096	47U	2200mm	800mm	IP20	1	Black Grey
21630-719	29U	1400mm	600mm	IP55	1	Black Grey
21630-423	38U	1800mm	800mm	IP20	1	Black Grey
21630-718	24U	1200mm	800mm	IP55	1	Black Grey
21630-717	24U	1200mm	600mm	IP55	1	Black Grey

CatalogNumber	Rack Height	Height	Width	Protection Rating	Package Quantity	Color
21630-097	52U	2450mm	800mm	IP20	1	Black Grey
21630-727	47U	2200mm	600mm	IP55	1	Black Grey
21630-726	42U	2000mm	800mm	IP55	1	Black Grey
21630-419	29U	1400mm	800mm	IP20	1	Black Grey
21630-092	42U	2000mm	600mm	IP20	1	Black Grey
21630-728	47U	2200mm	800mm	IP55	1	Black Grey

Table 2/2

Catalog Number	Color Code	Complies With	Finish	Type	Works With
21630-095	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP
21630-093	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP
21630-725	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-420	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP
21630-417	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP
21630-724	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-094	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP
21630-723	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-421	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP
21630-722	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-422	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP

Catalog Number	Color Code	Complies With	Finish	Type	Works With
21630-418	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP
21630-721	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-416	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP
21630-720	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-096	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP
21630-719	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-423	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP
21630-718	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-717	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-097	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP
21630-727	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-726	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-419	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP
21630-092	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Glass Door	Varistar CP
21630-728	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE