

Rail Four Post Terminal Block



FEATURES

Separates "clean" wiring from "dirty" wiring

Includes integrated test terminal

Includes slot for low-impedance busbar

Modular design for field assembly and future expansion

Meets AAR recommendations

SPECIFICATIONS

Table 1/2

Catalog Number	Length (L)	Depth (D)	Height (H)	A	B	Thread Size (TS)
B2700A2C1WH	133.35mm	25.4mm	31.75 mm	25.4 mm	60.3 mm	14" UNS
SBB2700A2B10	133.35mm	25.4mm	31.75 mm	25.4 mm	60.3 mm	14" UNS

Table 2/2

Catalog Number	Hardware Included
B2700A2C1WH	Yes
SBB2700A2B10	No

ADDITIONAL PRODUCT DETAILS

B2700A2C1WH kit includes: (1) terminal block, (1) offset test link, (15) 9/16" outer diameter copper flat washers, (9) zinc plated binding 14-24 UNS-2B hex nuts AAR, (5) nickel plated jam 14-24 UNS-2B hex nuts AAR, (2) #10X1 – 1/2" zinc plated screws, and (1) instruction print.

Four Post Terminal Blocks are components included in nVent ERICO pre-engineered and manufactured panels.

Design assistance is available for special applications. Contact your nVent ERICO representative for more details.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE