

# Rail Primary Power Surge Protector



## FEATURES

Modular design allows easy replacement of surge modules

Terminals provided within panel

Viewing window for safe inspection


Internal high interrupt capacity fusing for added safety

## SPECIFICATIONS

| Catalog Number                           | EPD100HZ120S           | EPD100HZ120V             | EPD100HZ120240V          |
|------------------------------------------|------------------------|--------------------------|--------------------------|
| Nominal System Voltage (Un)              | 120 VAC                | 120 VAC                  | 120/240 V                |
| Max Continuous Operating Voltage (Uc)    | 150 VAC                | 150 VAC                  | 150/300 VAC              |
| Max Discharge Current (Imax), Per Mode   | 15kA 8/20 $\mu$ s      | 15kA 8/20 $\mu$ s        | 15kA 8/20 $\mu$ s        |
| Nominal Discharge Current (In), Per Mode | 40kA 8/20 $\mu$ s      | 40kA 8/20 $\mu$ s        | 40kA 8/20 $\mu$ s        |
| Frequency                                | 0 - 100 Hz             | 0 - 100 Hz               | 0 - 100 Hz               |
| Voltage Protection Level (Up)            | 1200 V @ 15 kA         | 1200 V @ 15 kA           | 1400 V @ 15 kA           |
| Short Circuit Current Rating (SCCR)      | 25kA                   | 25kA                     | 25kA                     |
| Connection, Stranded                     | 2 - 50 mm <sup>2</sup> | 2.5 - 16 mm <sup>2</sup> | 2.5 - 16 mm <sup>2</sup> |
| Protection Modes                         | Differential<br>Common | Differential<br>Common   | Differential<br>Common   |

| Catalog Number     | EPD100HZ120S                                                            | EPD100HZ120V                                                            | EPD100HZ120240V                                                         |
|--------------------|-------------------------------------------------------------------------|-------------------------------------------------------------------------|-------------------------------------------------------------------------|
| Status Indication  | Mechanical flag                                                         | Mechanical flag                                                         | Mechanical flag                                                         |
| Technology         | MOV with thermal disconnect                                             | MOV with thermal disconnect                                             | MOV with thermal disconnect                                             |
| Humidity           | 0 - 90                                                                  | 0 - 90                                                                  | 0 - 90                                                                  |
| Temperature        | -40 to 80 °C                                                            | -40 to 80 °C                                                            | -40 to 80 °C                                                            |
| Enclosure Material | Metal                                                                   | Metal                                                                   | Metal                                                                   |
| Enclosure Rating   | NEMA®-4                                                                 | NEMA®-4                                                                 | NEMA®-4                                                                 |
| Depth (D)          | 116.84mm                                                                | 116.84mm                                                                | 116.84mm                                                                |
| Height (H)         | 203.2 mm                                                                | 203.2 mm                                                                | 203.2 mm                                                                |
| Width (W)          | 292.1 mm                                                                | 292.1 mm                                                                | 292.1 mm                                                                |
| Unit Weight        | 5.35 kg                                                                 | 5.35 kg                                                                 | 5.35 kg                                                                 |
| Complies With      | ANSI®/IEEE® C62.41.2-2002<br>Cat A, Cat B, Cat C<br>AREMA® requirements | ANSI®/IEEE® C62.41.2-2002<br>Cat A, Cat B, Cat C<br>AREMA® requirements | ANSI®/IEEE® C62.41.2-2002<br>Cat A, Cat B, Cat C<br>AREMA® requirements |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**