

TDS130 Replacement Module



CERTIFICATIONS



FEATURES

Replacement module for TDS130 Series

SPECIFICATIONS

Catalog Number	TDS130M150
Article Number	702432
Nominal System Voltage (Un)	120 - 150 VAC
Max Continuous Operating Voltage (Uc)	170 VAC
Voltage Protection Rating (VPR)	800 V @ 3 kA L-N 500 V @ 3 kA L+N-PE
Nominal Discharge Current (In)	8kA 8/20 μ s
Max Discharge Current (Imax), L-N	20kA 8/20 μ s
Max Discharge Current (Imax), L-PE	20kA 8/20 μ s
Frequency	0 - 100 Hz
Enclosure Material	UL® 94V-0 Thermoplastic

Catalog Number	TDS130M150
Temperature	-40 to 80 °C
Module Width	1 M
Depth (D)	49mm
Height (H)	45 mm
Width (W)	18 mm
Unit Weight	0.07 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE