

Front Panel, Front Anodized, Rear Conductive, Unshielded

Power Utilities

Front panel, unshielded, front anodized and rear conductive.



CERTIFICATIONS



FEATURES

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30847-469	5 U	84 HP	1	None	Screw-on Front	Anodized
30847-459	2 U	42 HP	1	None	Screw-on Front	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30847-460	2 U	63 HP	1	None	Screw-on Front	Anodized
30847-467	5 U	42 HP	1	None	Screw-on Front	Anodized
30847-468	5 U	63 HP	1	None	Screw-on Front	Anodized
30847-458	2 U	28 HP	5	None	Screw-on Front	Anodized
30838-043	3 U	4 HP	5	None	Screw-on Front	Anodized
30847-462	4 U	28 HP	5	None	Screw-on Front	Anodized
30847-466	5 U	28 HP	5	None	Screw-on Front	Anodized

Table 2/3

Catalog Number	Rear Finish	Treated Edges	Complies With	EMC Shielding	Height	Material
30847-469	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4 mm	Aluminum
30847-459	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	84 mm	Aluminum
30847-460	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	84 mm	Aluminum
30847-467	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4 mm	Aluminum
30847-468	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4 mm	Aluminum
30847-458	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	84 mm	Aluminum
30838-043	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum

CatalogNumber	Rear Finish	Treated Edges	Complies With	EMC Shielding	Height	Material
30847-462	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9 mm	Aluminum
30847-466	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4 mm	Aluminum

Table 3/3

Catalog Number	Product Type	Type	Width	Certifications
30847-469	Front Panel	Front Panel without Handle	426.4 mm	
30847-459	Front Panel	Front Panel without Handle	213 mm	
30847-460	Front Panel	Front Panel without Handle	319.7 mm	
30847-467	Front Panel	Front Panel without Handle	213 mm	
30847-468	Front Panel	Front Panel without Handle	319.7 mm	
30847-458	Front Panel	Front Panel without Handle	141.9 mm	
30838-043	Front Panel	Front Panel without Handle	20 mm	RoHS
30847-462	Front Panel	Front Panel without Handle	141.9 mm	
30847-466	Front Panel	Front Panel without Handle	141.9 mm	

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE