

Varistar CP Swing Frame for 600 mm Width

Power Utilities

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° movement and flexible pivot point.

FEATURES

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks (maximum depth 200 mm)

120° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Color	Color Code	Height	Material	Product Type
21630-668	24 U	Black Grey	RAL 7021	1200 mm	Steel	Cabinet/Rack Frame
21630-670	29 U	Black Grey	RAL 7021	1400 mm	Steel	Cabinet/Rack Frame
21630-672	33 U	Black Grey	RAL 7021	1600 mm	Steel	Cabinet/Rack Frame
21630-674	38 U	Black Grey	RAL 7021	1800 mm	Steel	Cabinet/Rack Frame
21630-676	42 U	Black Grey	RAL 7021	2000 mm	Steel	Cabinet/Rack Frame
21630-678	47 U	Black Grey	RAL 7021	2200 mm	Steel	Cabinet/Rack Frame

Table 2/2

Catalog Number	Protection Rating	Width
21630-668	IP20	600 mm
21630-670	IP20	600 mm
21630-672	IP20	600 mm
21630-674	IP20	600 mm
21630-676	IP20	600 mm
21630-678	IP20	600 mm

ADDITIONAL PRODUCT DETAILS

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE