

On Demand Stock Panels: NGC-40



nVent RAYCHEM NGC-40 On Demand Stock Panels offer rapid delivery of optimized best-in-class standard panel configurations for customer projects. Panels are built with quality components including premium RAYCHEM controllers for use in hazardous and nonhazardous areas. Many configurations have C1D2 circuit breakers and Type 4X stainless steel enclosures.

FEATURES

Improve efficiency and reduce lead times by using standardized EHT controller & panel designs

Broad selection of configurations available immediately with best-in-class advanced control options

Consistent design with time-tested quality for your project

SPECIFICATIONS

Table 1/1

Catalog Number	Circuit Breaker Voltage Rating	Main Circuit Breaker Current Rating	Touchscreen Included	Control Relay Type	Voltage Rating
101723-001			No	Solid State	277 – 480 V
101723-003	277 V	70 A	No	Solid State	277 – 480 V
101723-002	277 V	50 A	No	Solid State	277 – 480 V
101723-005	277 V	175 A	No	Solid State	277 – 480 V
101723-004	277 V	125 A	No	Solid State	277 – 480 V

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT