

Elexant 3500i Electronic Thermostat



The Raychem Elexant 3500i is a family of compact, full-featured, electronic thermostats for heat tracing control and monitoring in freeze protection and process temperature applications. Designed from a common hardware platform, the Elexant 3500i offers multiple variants with different features to allow the user flexibility in tailoring their heat tracing needs. Available features include: alarm relay, RS-485 and Bluetooth connections, load sensing, ground fault detection, automated heat trace system check, mobile application for wireless configuration, and more. The Elexant 3500i is suitable for hazardous and nonhazardous locations, and can be wall mounted or pipe mounted.

FEATURES

Multiple variants to allow flexibility for different heat-tracing requirements

Options including dry contact alarm relay, RS-485 and Bluetooth communications, load current detection, ground fault detection and trip, as well as the ability to configure as a thermostat or limiter

Power Connection and Thermostat in one kit

250k cycle endurance for long life

Approved for up to 32A and 277Vac

Suitable for extreme environments with an ambient operating temperature from -55°C to 60°C

SPECIFICATIONS

NEMA Rating:	4X
Max Power Supply Input Wire Size:	16 mm ²
Max Ground Terminal Wire Size:	16 mm ²
Max Heating Cable Output Wire Size:	16 mm ²

Control Max Current:	32A @ 40°C, derated to 28A @ 50°C and 24A @ 60°C ambient operating temperature
Depth:	90 mm
Width:	206 mm
Control Max Voltage:	277 VAC Nominal, 50/60Hz
Relative Humidity:	0% to 90%, Noncondensating
IP Rating:	IP66
Control Algorithms:	On/Off, Always On, Always Off
Hazardous Area:	Yes
Intrinsically Safe Barriers on RTD Inputs:	Yes
Temperature Control Range:	-55 to 550 °C
Operating Temperature:	-55 to 60 °C
Temperature Alarm:	-60 to 600 °C

Table 1/2

Catalog Number	Height	Autocycle	Communication	Communication Protocol	Control Relay Type	Ground Fault Alarm
2000002454	183 mm		Yes	Modbus RTU	Single-Pole Hybrid	
2000002626	282 mm		Yes	Modbus RTU	Single-Pole Hybrid	
2000002924	183 mm	24 h	Yes	Modbus RTU	Double-Pole, Hybrid	30 mA min
2000003749	183 mm				Single-Pole Hybrid	
2000003750	183 mm				Single-Pole Hybrid	
2000003751	183 mm	24 h	Yes	Modbus RTU	Double-Pole, Hybrid	
2000003757	282 mm				Single-Pole Hybrid	
2000003758	282 mm				Single-Pole Hybrid	
2000003759	282 mm	24 h	Yes	Modbus RTU	Double-Pole, Hybrid	
2000003760	282 mm	24 h	Yes	Modbus RTU	Double-Pole, Hybrid	30 mA min

Table 2/2

Catalog Number	Mounting	RS-485 Cable Type	RS-485 Max Cable Length	Safety Limiter
----------------	----------	-------------------	-------------------------	----------------

2000002454	Wall	One 2-Wire, Shielded Twisted Pair	1200 m	Configurable as Limiter
2000002626	Pipe	One 2-Wire, Shielded Twisted Pair	1200 m	Configurable as Limiter
2000002924	Wall	One 2-Wire, Shielded Twisted Pair	1200 m	Configurable as Limiter
2000003749	Wall			
2000003750	Wall			
2000003751	Wall	One 2-Wire, Shielded Twisted Pair	1200 m	Configurable as Limiter
2000003757	Pipe			
2000003758	Pipe			
2000003759	Pipe	One 2-Wire, Shielded Twisted Pair	1200 m	Configurable as Limiter
2000003760	Pipe	One 2-Wire, Shielded Twisted Pair	1200 m	Configurable as Limiter

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT