

EuropacPRO 19" Subrack Kit for Backplane, Rugged, Shielded

Subrack with reinforced horizontal rails and side panels for backplane mounting.



CERTIFICATIONS



FEATURES

Subrack with side panel and horizontal rail, type R "rugged" with 3 hole fixing for increased stability (+60% compared to 2 hole fixing of "Heavy" rails)

Aluminum construction

Rear horizontal rail for backplane mounting with insulation strip. Special adaptor rails allow conduction cooled assemblies to be fitted

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, -102, -103, IEEE 1101.1, IEEE 1101.10

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Shock and vibration tested to MIL 167, IEC 61587 DL 3, MIL 810 G, MIL 901D. Shock and vibration resistant in all three axial directions.

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available. Subrack with telescoping slides can be adopted for cabinet mounting on request

Horizontal rail type "rugged"

SPECIFICATIONS

Material:	Aluminum
Finish:	Anodized; Passivated
Product Type:	Subrack/Chassis
EMC Shielding:	Yes

Table 1/3

Catalog Number	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	Gasket Type
24567-149	3U	295mm	1	Backplane	160mm	Textile EMC
24567-449	6U	295mm	1	Backplane	160mm	Textile EMC

Table 2/3

Catalog Number	Shock and Vibration Tolerance	Handle Included	Mounting	Complies With	Rack Width	Static Load
24567-149	25g (force)	Yes	Rack	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, MIL 167, MIL 810 G, MIL 901 D, IEC 61587 DL3	84HP	25kg
24567-449	25g (force)	Yes	Rack	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, MIL 167, MIL 810 G, MIL 901 D, IEC 61587 DL3	84HP	25kg

Table 3/3

Catalog Number	Quick Ship
24567-149	No
24567-449	No

ADDITIONAL PRODUCT DETAILS

Test reports online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE