

Inpac 19" Chassis



The nVent SCHROFF Inpac chassis, provides electronics protection for 19" and individual electronic assemblies and also can be used for desktop applications.

CERTIFICATIONS



FEATURES

Grounding/earthing kit optional

RAL 7030 powder coat finish

For assembly with 19" components or individually with mounting plates

Three rows of ventilation slots in base for air inlet

Aluminum construction with die-cast front and rear frames

IP 20, in accordance with IEC 60529

External dimensions in accordance with IEC 60297-3-101

Grounding/earthing connectors to: DIN EN 50178/VDE 0160, DIN EN 62368-1/VDE 0805, DIN EN 61010-1/VDE 0411 part 1, DIN EN 61010-1A2/VDE 0411 part 1/A1

Modifications such as cutouts or paint available

SPECIFICATIONS

Rack Width: 84HP

Product Type: Case

Product Family: Inpac

Table 1/2

Catalog Number	Rack Height	Depth	Package Quantity	Mounting	Complies With	EMC Shielding
10828-151	3U	254.5mm	1	Rack	IEC 60297-3-101	No
10828-152	3U	314.5mm	1	Rack	IEC 60297-3-101	No
10828-153	3U	374.5mm	1	Rack	IEC 60297-3-101	No
10828-154	3U	434.5mm	1	Rack	IEC 60297-3-101	No
10828-156	4U	254.5mm	1	Rack	IEC 60297-3-101	No
10828-157	4U	314.5mm	1	Rack	IEC 60297-3-101	No
10828-158	4U	374.5mm	1	Rack	IEC 60297-3-101	No
10828-159	4U	434.5mm	1	Rack	IEC 60297-3-101	No
10828-168	6U	374.5mm	1	Rack	IEC 60297-3-101	No
10828-169	6U	434.5mm	1	Rack	IEC 60297-3-101	No
10828-171	2U	254.5mm	1	Rack	IEC 60297-3-101	No
10828-172	2U	314.5mm	1	Rack	IEC 60297-3-101	No
10828-173	2U	374.5mm	1	Rack	IEC 60297-3-101	No

Table 2/2

Catalog Number	Finish	Material	Static Load	Quick Ship
10828-151	Powder Coated	Aluminum, Steel	15kg	No
10828-152	Powder Coated	Aluminum, Steel	15kg	No
10828-153	Powder Coated	Aluminum, Steel	15kg	No

Catalog Number	Finish	Material	Static Load	Quick Ship
10828-154	Powder Coated	Aluminum, Steel	15kg	No
10828-156	Powder Coated	Aluminum, Steel	15kg	No
10828-157	Powder Coated	Aluminum, Steel	15kg	No
10828-158	Powder Coated	Aluminum, Steel	15kg	No
10828-159	Powder Coated	Aluminum, Steel	15kg	No
10828-168	Powder Coated	Aluminum, Steel	15kg	No
10828-169	Powder Coated	Aluminum, Steel	15kg	No
10828-171	Powder Coated	Aluminum, Steel	15kg	No
10828-172	Powder Coated	Aluminum, Steel	15kg	No
10828-173	Powder Coated	Aluminum, Steel	15kg	No

ADDITIONAL PRODUCT DETAILS

Max. installation space when fitting 19" components is 75 HP.

Scope of delivery includes screws to fix rear and front panels.

Cover and base plate available in other colors.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE