

# Inpac Front Panel, Bottom-Hinged

The bottom hinged front panel can be combined with the Inpac cases.



## CERTIFICATIONS



## FEATURES

The bottom hinged front panel can be combined with the Inpac cases

## SPECIFICATIONS

|                        |             |
|------------------------|-------------|
| <b>Depth:</b>          | 2.5mm       |
| <b>Material:</b>       | Aluminum    |
| <b>Finish:</b>         | Anodized    |
| <b>Accessory Type:</b> | Front panel |
| <b>Product Type:</b>   | Front Panel |

Table 1/2

| Catalog Number | Rack Height | Package Quantity | Front Finish | Rear Finish | Treated Edges | EMC Shielding |
|----------------|-------------|------------------|--------------|-------------|---------------|---------------|
| 30828-085      | 2U          | 1                | Anodized     | Anodized    | No            | No            |
| 30828-097      | 6U          | 1                | Anodized     | Anodized    | No            | No            |

| CatalogNumber | Rack Height | Package Quantity | Front Finish | Rear Finish | Treated Edges | EMC Shielding |
|---------------|-------------|------------------|--------------|-------------|---------------|---------------|
| 30828-091     | 4U          | 1                | Anodized     | Anodized    | No            | No            |
| 30828-088     | 3U          | 1                | Anodized     | Anodized    | No            | No            |

| Table 2/2      |         |       |            |
|----------------|---------|-------|------------|
| Catalog Number | Height  | Width | Quick Ship |
| 30828-085      | 76mm    | 437mm | No         |
| 30828-097      | 253.8mm | 437mm | No         |
| 30828-091      | 165mm   | 437mm | No         |
| 30828-088      | 120.5mm | 437mm | No         |

### ADDITIONAL PRODUCT DETAILS

Please order hinge for front panel separately.

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

#### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

#### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

#### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

#### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE