

Rail Web Mold Clamp, Adjustable



FEATURES

Adjusts for a wide span of uses including frogs and switches

Lightweight and easy to use

Can also be used on standard (single) rail

SBC105RR provides improved safety with non-sharp profiles and reflecting tape for high visibility

SPECIFICATIONS

Table 1/1

Catalog Number	Welder Style	Mold Size	Jaw Opening
SBC105RR	T21	60 mm	648 mm Max
PBC105P	T20	89 mm	600 mm Max
SBC105R	T21	76 mm	648 mm Max

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE