

SBHM Hollow Core Metal Tipped Rail Drill Bit



FEATURES

Designed for high-speed drilling applications

Withstands approximately 50 uses

Drill bits can be reground approximately five times

3/4" (19 mm) Weldon shank

Can be used on all rail types

Optional adaptor ADAPSBHM (716172) extends the length of the drill bit

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Material	Finish	Drill Bit Diameter (Ø)	Length (L)
SBHM2370	716322	High-Speed Steel	TIALN Coating	23 mm	63mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE