

Brace Terminals Flat, W060



Connection terminals that secure flat conductors to the busbars.

INDUSTRY STANDARDS

UL

GL

DNV-GL

DNV-GL

FEATURES

Description: Terminal for flat conductors with captive clamping screws, conductor can be overlapped, indication of nominal cross-section and tightening torque noted on the terminal. Contact between conductor and busbar via contact block.

Rated voltage: 690 V

For busbars: 20, 25, 30 × 5, 10

Approvals: UL, GL, DNV-GL

SPECIFICATIONS

Table 1/1						
Catalog Number	Height	Width	Depth	Material	Finish	Package Quantity
01319	43mm	38mm	88mm	Mild Steel	Plated	6
01759	43mm	40mm	98mm	Mild Steel	Plated	3

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE