

# Cable Entry Gland Plate Blind Cover, CEAB



Blind cover-to-cover opening for CEP and CCF cable entries.

## INDUSTRY STANDARDS

UL94 V-0 Flammability; File No. E61997

NEMA Type 1, 12, 4X (indoor only)

CE

IP66

## FEATURES

Description: Blind cover-to-cover openings for CEP and CCF cable entries. Mounted over the opening by using screw fixation.

Finish: Black

Flammability: UL94 V-0

Material: Polyamide 6.6 / TPE

Pack quantity: 10 pcs

Protection: IP66

Temperature resistance: -40°C to +120°C

SPECIFICATIONS

| Table 1/1      |        |       |        |                  |          |           |
|----------------|--------|-------|--------|------------------|----------|-----------|
| Catalog Number | Height | Width | Depth  | Product Family   | Material | Finish    |
| CEAB1024       | 55mm   | 126mm | 11.5mm | Cable management | Plastic  | Untreated |
| CEAB816        | 55mm   | 126mm | 11.5mm | Cable management | Plastic  | Untreated |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE