

Crossboard Adapter Slim, WOCB



CrossBoard adapter with fuse-carrier 16 A. Makes mounting of measuring and mounting realays easy.

INDUSTRY STANDARDS

UL

IEC

FEATURES

Description: 3 pole adapter, 16 A. One fixed mounting rail, with fuse-carrier 10 × 38 / Class CC. With cables 2.5 mm².

Rated voltage: 690 V

Rated current: 16 A

Power dissipation at 80% load: 2.6 W

Dimensions: 22.5 × 160 × 85 mm

Pack quantity: 1 pc.

Approvals: IEC,UL

SPECIFICATIONS

Table 1/1						
Catalog Number	Height	Width	Depth	Material	Finish	Color
36009	22.5mm	160mm	85mm	Plastic	Smooth Matte	Light Gray

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE