

Gland plate with knockouts, AFK



The required number of holes for cable entries can be easily knocked out of this steel gland plate to allow for the cabling required.

FEATURES

Description: Gland plates with knock-outs according to table.

Material: 1.4 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 piece.

SPECIFICATIONS

Thickness:	1.4mm
Color:	Light Gray
Material:	Mild Steel
Finish:	Powder Coated
Color Code:	RAL 7035

Table 1/1

Catalog Number	Height	Width	Depth	Knockout Pattern	Gland Plate Type	Gland Plate Opening Width
AFK11R5	242mm	128mm	3mm	(4) M16, (5) M20, (2) M25, (2) M32	1	210mm
AFK11SR5	242mm	88mm	3mm	(4) M16, (3) M20	1S	210mm
AFK21R5	342mm	128mm	3mm	(9) M16, (5) M20, (4) M25, (2) M32	2	310mm
AFK21SR5	342mm	88mm	3mm	(6) M16, (3) M20, (1) M25	2S	310mm
AFK31R5	442mm	128mm	3mm	(18) M16, (5) M20, (4) M25, (2) M32	3	410mm
AFK31SR5	442mm	88mm	3mm	(9) M16, (4) M20, (1) M25	3S	410mm
AFK41R5	542mm	128mm	3mm	(27) M16, (5) M20, (4) M25, (2) M32	4	510mm
AFK42R5	542mm	88mm	3mm	(18) M16, (14) M20, (3) M25, (1) M32	4	510mm
AFK12R5	242mm	128mm	3mm	(12) M16, (1) M25, (1) M32	1	210mm
AFK22R5	342mm	128mm	3mm	(21) M16, (1) M32, (1) M25	2	310mm
AFK32R5	442mm	128mm	3mm	(21) M16, (10) M20	3	410mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE