

Transposition Sections Lay-in Hinged-Cover



Lay-in Hinged-Cover Transposition Sections are used when it is necessary to rotate the open side of the wireway run by 90 degrees and still retain the lay-in feature.

INDUSTRY STANDARDS

Certified by Canadian Standards Association.

FEATURES

Lay-in Hinged-Cover Transposition Sections are used when it is necessary to rotate the open side of the wireway run by 90 degrees and still retain the lay-in feature

SPECIFICATIONS

Color Code: ANSI 61
Finish: Galvanized; Powder Coated
Color: Gray
Material: Mild Steel

Table 1/1

Catalog Number	Type	Height	Width	Thickness	Sealing Plate Quantity	Sealing Plate Type
F22LE9KOKT	Transposition Section	64mm	64mm	1.9mm	1	Flat
F22LE9KT	Transposition Section	64mm	64mm	1.9mm	1	Flat
F22LKOKT	Transposition Section	64mm	64mm	1.9mm	1	Flat
F22LKT	Transposition Section	64mm	64mm	1.9mm	1	Flat
F44LE9KOKT	Transposition Section	102mm	102mm	1.9mm	1	Flat
F44LE9KT	Transposition Section	102mm	102mm	1.9mm	1	Flat
F44LKOKT	Transposition Section	102mm	102mm	1.9mm	1	Flat
F44LKT	Transposition Section	102mm	102mm	1.9mm	1	Flat
F66LE9KOKT	Transposition Section	152mm	152mm	1.9mm	1	Flat
F66LE9KT	Transposition Section	152mm	152mm	1.9mm	1	Flat
F66LKOKT	Transposition Section	152mm	152mm	1.9mm	1	Flat
F66LKT	Transposition Section	152mm	152mm	1.9mm	1	Flat
F88LE9KOKT	Transposition Section	203mm	203mm	1.9mm	1	Flat
F88LE9KT	Transposition Section	203mm	203mm	1.9mm	1	Flat

ADDITIONAL PRODUCT DETAILS

Each sealing plate also includes one gasket and one set of screws to join sections.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE